

PNEUMATIC IMPACT WRENCHES

Compact impact wrench

Powerful, compact and lightweight!



1/2"


- Ultra-compact and lightweight wrench.
- High power to size ratio
- Double-hammer mechanism gives better balance and fewer vibrations.

IDEAL FOR:

Dismantling:
gearboxes, ball joints, strut rods, transmissions, exhaust pipes, etc.



COMPACT



Adjustable
tightening
torque

► Compact impact wrench

- Guaranteed static torque
- Max. torque: 380 Nm
- ΔΔ : 1,34 kg.

"Butterfly" impact wrench

The world's smallest impact wrench!

3/8"

USES:

- Accessing difficult-to-reach places
- Removal of gearboxes, sumps, dashboards, etc.

- Ultra-compact wrench
- Lightweight.
- 4 torque settings
- One-handed reverse switch operation
- Double-hammer mechanism.
- Speed controller.

AVAILABLE
NOVEMBER 2009
IN UK



NJ.14FPB
3148518337236



► "Butterfly" impact wrench set

- 3/8" square drive.
- Guaranteed static torque: 47 Nm.
- Max. torque: 60 Nm.
- Supplied in a plastic case BP.112 with 12 3/8" drive impact sockets, 6 to 19 mm + plastic tray.

ΔΔ : 0,46 kg.



► New pneumatic accessories

AVAILABLE
NOVEMBER 2009
IN UK

	Description
N.820	1/2" gas female quick coupler
N.630	3/8" gas female quick coupler
N.651	1/2" gas male fitting
N.650	3/8" gas male fitting
N.633	1/4" gas male fitting



	Description
N.644	Polyurethane spiral hose Ø 8 x 12, max. length 8 m. Fitted with a 3/8" gas swivel connector on the tool end, a 3/8" gas fixed connector on the air supply end and a 3/8" gas female threaded 6 mm adapter



	Description
N.641	Opening dia. x Hose dia. Ø 8 x 14 mm
N.841	Ø 10 x 16 mm
N.643	Ø 10 x 16 mm
N.842	Ø 16 x 22 mm

