




TE Internal #: 1761015-3  
SFP, Cage Assembly, Signal, Operating Temperature Range -55 – 85 °C [-67 – 185 °F], Data Rate (Max) 4 Gb/s, 6 Ports, Port Matrix Configuration 1 x 6  
[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages



Form Factor: **SFP**  
Pluggable I/O Product Type: **Cage Assembly**  
Sealable: **No**  
Circuit Application: **Signal**  
Operating Temperature Range: **-55 – 85 °C [ -67 – 185 °F ]**

Features

Product Type Features

|                            |               |
|----------------------------|---------------|
| Cage Type                  | Ganged        |
| Form Factor                | SFP           |
| Pluggable I/O Product Type | Cage Assembly |
| Sealable                   | No            |

Configuration Features

|                           |       |
|---------------------------|-------|
| Number of Ports           | 6     |
| Port Matrix Configuration | 1 x 6 |

Electrical Characteristics

|                 |        |
|-----------------|--------|
| Data Rate (Max) | 4 Gb/s |
|-----------------|--------|

Termination Features

|                           |                          |
|---------------------------|--------------------------|
| Termination Method to PCB | Through Hole - Press-Fit |
|---------------------------|--------------------------|

Usage Conditions

|                             |                           |
|-----------------------------|---------------------------|
| Operating Temperature Range | -55 – 85 °C[-67 – 185 °F] |
|-----------------------------|---------------------------|

Operation/Application



|                              |                               |
|------------------------------|-------------------------------|
| Pluggable I/O Applications   | SFP                           |
| Circuit Application          | Signal                        |
| Other                        |                               |
| Included Lightpipe           | No                            |
| EMI Containment Feature Type | Internal/External EMI Springs |

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                            |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2185239-5  
[ASSY, SEATING TOOL, SFP+](#)

Customers Also Bought



TE Part #1761013-3  
[SFP 1X6 LIGHT PIPE ASSY](#)




TE Part #5223985-6  
[UPM KEYED GUIDE PIN #6-32](#)




TE Part #2201945-1  
[RECEPTACLE ASSEMBLY, 5 PAIR, 8 COLUMN](#)



TE Part #1542618-2  
[XFP MSA SAN APPLICATION](#)




TE Part #5352106-1  
[Z-PACK/A RAMH.110P.](#)




TE Part #100526-9  
[Z-PACK F.CODING KEY](#)



TE Part #5747714-2  
[37 RCPT ACT PIN/MS MED INSRT](#)



TE Part #1554570-2  
[MODULE FEMALE GUIDE, UNIVERSAL POWER](#)



TE Part #1746790-2  
[GROUND RETURN LOWER SHIELD TYPE A,PB-FRE](#)



TE Part #176415-1  
[U-M-N-L D-TYPE PLUG KIT 4P](#)

Documents

Product Drawings

[SFP 1X6 CAGE ASSY W/ KAPTON TAPE, PF](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1761015-3\\_F.2d\\_dxf.zip](#)





English

Customer View Model

[ENG\\_CVM\\_CVM\\_1761015-3\\_F.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1761015-3\\_F.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English