## SIEMENS

## Data sheet

## 3RK1902-1DA00

M12 socket for PROFIBUS angled, 5-pole, B-coded screw terminal No terminating resistor



General technical data		
ampacity per pin maximum	А	4
operating voltage maximum	V	125
flow resistance maximum	Ω·m	3
surge voltage resistance rated value	kV	0.8
Mechanical data		
type of connection technology		Screw terminals
connector type		Socket
connector coding of the M12 circular connector		В
type of cable outlet		angled
number of poles		5
connectable conductor cross-section for flexible conductor maximum	mm²	0.75
diameter of inlet opening	mm	6 8
material		
• of the contact		Brass, bronze
<ul> <li>of contact coating</li> </ul>		Gold
<ul> <li>of connector fixed part</li> </ul>		Polyamide
• of the enclosure		Zinc diecast, nickel-plated
depth	mm	20
height	mm	54
width	mm	43
type of strain relief		Pressure screw, pinch ring
mechanical service life (mating cycles)		100
type of plug interlock		M12 x 1 thread
Ambient conditions		
ambient temperature		
during storage	°C	-25 +85
<ul> <li>during operation</li> </ul>	°C	-25 +85
protection class IP		IP67
chemical resistance		
• to mineral oil		conditional, must be checked relative to the application
• to water		conditional, must be checked relative to the application
• to grease		conditional, must be checked relative to the application
degree of pollution		3
Certificates/ approvals		
certificate of suitability		
CSA approval		No
RoHS conformity		Yes

• CCC	No	
IEC approval	No	
cUL approval	No	
• C-Tick	No	
Further information		

Siemens has decided to exit the Russian market (see here).

https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

https://support.industry.siemens.com/cs/ww/en/view/109813875

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1902-1DA00

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1902-1DA00

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RK1902-1DA00

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RK1902-1DA00&lang=en

last modified:

8/29/2023 🖸