

LG7D12V716

Enclosed DOL starter, TeSys LG, 9-14A, 400V
AC coil, including 1 LC1D, GV2ME, emergency
stop, 2 pushbuttons, GVAX

Main

Range	TeSys
Product name	TeSys LG
Device short name	LG7D
Product or component type	Enclosed DOL starter
Device application	Safety
Utilisation category	AC-3
Device composition	Contactors Circuit-breaker
Motor power kW	3 kW at 220/230 V AC 50/60 Hz 5.5 kW at 400/415 V AC 50/60 Hz 5.5 kW at 440 V AC 50/60 Hz
Thermal protection adjustment range	9...14 A
[Uc] control circuit voltage	400 V AC 50/60 Hz
Control type	Push-button start white I Push-button stop black O Mushroom head push-button emergency stop red

Complementary

Standards	IEC 60204-1 IEC 60947-4-1
Product certifications	CE[RETURN]UKCA
Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Height	165 mm
Depth	146 mm
Net weight	1.6 kg
Width	175 mm

Environment

Material	Polycarbonate
IK degree of protection	IK07 conforming to IEC 60529
IP degree of protection	IP55 conforming to IEC 60529
Environmental characteristic	Standard environment

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins