

Rotary Hammer LXT®

DHR242

18V • SDS-PLUS • 24 mm • 2.0 J

Professional brushless, three-mode rotary hammer

An efficient rotary hammer for SDS-PLUS bits with an anti-vibration handle. Suitable for impact and unstressed drilling, plus chipping. Speed range of 0 – 950 min⁻¹. Impact energy of 2.0 J and max. drilling capacity of 24 mm in concrete.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Impact Energy	2,0 J
Optimum Drilling Diameter Range in Concrete	4 - 16 mm
Max. Drilling Diameter in Concrete	24 mm
Max. Drilling Diameter in Wood	27 mm
Max. Drilling Diameter in Steel	13 mm
Impacts per Minute (IPM)	0 - 4700 min ⁻¹
No load speed	0 - 950 min ⁻¹
Drilling diameter with TCT core bit	54 mm
Adapted for SDS-PLUS bits	✓
Tool weight with battery	3,1 - 3,8 kg
Electronic brake	✓

User benefits

- Brushless maintenance-free and long-life motor
- Low power consumption thanks to brushless motor
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing