

Backpack garden sprayer LXT®

DUS158

18V • 15 L

Battery powered garden sprayer.

Battery powered garden sprayer with 18V voltage. Easy to set up and light to carry. Very quiet running sound. Large spray volume on a single full battery charge.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Maximum Flow Rate	1,7 L/min
Max Pressure	5 bar
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	5,9 - 6,2 kg
Product Dimensions (L x W x H):	325 x 237 x 517 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Hose length	1,7 m
Product net weight	5,1 kg
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Container Capacity	15 L

User benefits

- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Dust and water resistance with IP54 rating for increased durability
- Lever at hand for easier operation
- Large spray volume on a single full battery charge
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing