

Product datasheet

Specifications



Data socket, New Unica, RJ45 CAT 6 STP, straight, click, shuttered, 2 module, white

NU341918

Main

Range	New Unica
Product or component type	Data socket
Device application	Communication
Device presentation	Mechanism with cover plate
Colour tint	White (RAL 9003)
Data socket type	RJ45 8 contact(s) Cat.6 < 250 MHz
Provided equipment	Protective flap Label holder

Complementary

Communication network type	1000BASE-TX
Communication port protocol	ATM 1200 Mbps
Number of modules	2 modules
Socket number	1
Type of footprint	Infraplus
Connector type	S-One
Cable shielding type	S/FTP
Organization of wire	Shielded twisted pair
Connections - terminals	Click
Device mounting	Flush
Fixing mode	Clip-in
Installation direction	Straight
Material	Thermoplastic ABS-UV stabilised: central plate
Quantity per set	1
Depth	40.5 mm
Width	45 mm
Height	45 mm
Embedding depth	40.5 mm

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
-------------------------------	---

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-5...35 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	4.500 cm
Package 1 Length	4.500 cm
Package 1 Weight	45.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.500 cm
Package 2 Width	14.000 cm
Package 2 Length	26.000 cm
Package 2 Weight	517.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	100
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.600 kg

Contractual warranty

Warranty (in months)	18
----------------------	----

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	0.3 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	0.2 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.1 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Average percentage of recycled plastic content	40 %
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	89f48f58-8743-4a8c-aad2-c796c3e70cb3
EU RoHS Directive	Compliant
REACH Regulation	Free of Substances of Very High Concern above the threshold

Use Longer

 Lifetime extension	
Repair	No

Use Again

 Repack and remanufacture	
Recyclability potential, in %	41
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative







