

## FEATURES

- Momentary foot switch controller
- Contact rating 16A 125V-250Vac
- Cast aluminum body and treadle
- Base plate with non-skid feet
- 4 bolt holes
- Single M20 entry
- Sealed to IP68 – protected from dust and water
- Range comes guarded or unguarded – guard covers entire foot switch for extra safety to the user
- Classic IV Foot Switch

## RS PRO Medium Duty Momentary Foot Switch - Aluminium Case Material, SP- CO, 16 A @ 250 V ac Contact Current, 250V

RS Stock No.: 116-805



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description ATTRIBUTE 1

RS PRO momentary medium duty foot switches which have been designed with an integral non-slip base pad or feet. These switches are manufactured from aluminium and have Single Pole Double Throw (SPDT) contacts. These foot controller pedals are sealed to IP68 and are ideal for industrial applications.

This range of foot switches includes the following types:

116-798 - Twin Pedal, Guarded, Momentary, SPDT

116-805 – Single, Guarded, Momentary, SPDT

116-811 - Twin Pedal, Unguarded, Momentary SPDT

## General Specifications

<b>Contact Configuration</b>	SP-CO
<b>Switch Operation</b>	Momentary
<b>Case Material</b>	Aluminium
<b>Switch Environment</b>	Medium Duty
<b>Guard Cover</b>	Yes
<b>Colour</b>	Black body, silver treadle & Alert Orange guard
<b>Applications</b>	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
<b>Cable Connection</b>	1 x M20 entry

## Electrical Specifications

<b>Contact Voltage Rating (AC)</b>	250V
<b>Contact Current Rating</b>	16A @ 250V ac

## Mechanical Specifications

Length	177.8mm
Height	113.16mm
Dimensions	177.8mm x 152.4mm x 113.16mm
Width	152.4mm
Weight	2.7kg

## Protection Category

IP Rating	IP68
-----------	------

## Approvals

Standards Met	EN 60529
Compliance/Certifications	IEC 601-2-2, RoHS





**Size**

(See below)

