

## VENICUTB07



ANTISTATIC CARBON/DELTANOCUT® KNITTED GLOVE - NITRILE MICRO-FOAM COATED PALM - GAUGE 18  
Ref. VECUTB07



### Product specifications

DELTAnocut® high performance fibre and carbon fibre. Nitrile micro-foam coating on palm and fingertips.  
Gauge 18.

Support: DELTAnocut® high performance fibre and carbon fibre.  
Coating: nitrile micro foam.

**COLOUR**

Black

**SIZE**

06, 07, 08, 09, 10, 11

## Product Use - Risks



Wearing



CUTTING



Antistatic



Heat



Construction / Civil engineering



Second work / craftman



Light industry



Services / Logistics

Product's highlights & user's benefits



Solvent-free coating

Suitable for sensitive people  
Respectful of the environment  
Ideal for the automotive industry  
No traces on the objects handled



Nitrile micro-foam coating

Good resistance to abrasion  
Extra fine finish for increased dexterity



Gauge 18

Very good dexterity and work finesse



Tested before and after washing: unchanged performance

Increased lifespan for better profitability

Carbon fibre

High electrostatic dissipation to reduce the risk of explosion



Cut level B

## Certifications and Standards



### REGULATION (EU) 2016/425

EN ISO 21420:2020 General requirements

EN388:2016+A1:2018 Protective gloves against mechanical Risks (Levels obtained on the palm)



- 3: Resistance to abrasion (from 1 to 4)
- X: Resistance to cutting (from 1 to 5)
- 3: Resistance to tear (from 1 to 4)
- 1: Resistance to puncture (1 to 4)
- B: Resistance to cutting by sharp objects (TDM EN ISO 13997) (from A to F)

EN407:2020 Protective gloves against Heat & Fire risks (X = Unrealized test)



- X: Flame spread resistance.
- 1: Contact heat resistance (from 1 to 4)
- X: Convective heat resistance (1 to 4)
- X: Radiant heat resistance (from 1 to 4)
- X: Small splashes of molten metal (from 1 to 4)
- X: Large quantities of molten metal (from 1 to 4)



EN16350:2014 Protective gloves - Electrostatic properties.

- 3.44 x 10E5: Vertical resistance in ohms ( $\Omega$ ) according to EN1149-2:1997


### USA STANDARDS



ANSI-ISEA 105:2016 Hand protection

- A2: Resistance to cutting by sharp objects (from A1 to A9)

## References

References	Bar code	COLOUR	SIZE		
VECUTB07GR06	3295249264239	Black	06	60	12
VECUTB07GR07	3295249264420	Black	07	60	12
VECUTB07GR08	3295249264437	Black	08	60	12
VECUTB07GR09	3295249264444	Black	09	60	12
VECUTB07GR10	3295249264451	Black	10	60	12
VECUTB07GR11	3295249264468	Black	11	60	12