



1" gun-type impact wrench - short anvil - high performance



Description:

- Dual hammer mechanism for tool durability.
- 2 stage trigger for improved control.
- One hand forward reverse switch with two settings in both directions.
- Rubber over molded grip insulating against cold and vibrations.
- Rubber bumper protecting the motor housing.
- 360° adjustable handle for improved comfort.
- Safe: Dual socket retainer: ring retainer hole to use a safety pin.
- Exhaust blows air away from the operator for comfort of use.



	Height H [mm]	Length L [mm]	Length L1 [mm]	Torque NM. [Nm]	Vibration Level [m/s ²]	Maximum Speed [rpm]	Weight [Kg]
NM.3000F	239.0	279.0	102.0	3390.0	10,6 (K=1,55)	5000.0	6.9