



### Contact characteristics

|  |   |        |
|--|---|--------|
| Number of poles  | Nr.   | 4      |
| Rated insulation voltage $U_i$ IEC/EN  | V   | 1000   |
| Rated impulse withstand voltage $U_{imp}$                                      | kV  | 8      |
| Operational frequency  | min   | Hz 25  |
|  | max   | Hz 400 |
| IEC Conventional free air thermal current $I_{th} \leq 40^\circ\text{C}$       | A   | 500    |
| Operational current $I_e$  | AC-1 ( $\leq 40^\circ\text{C}$ )                  | A 500  |
|  | AC-1 ( $\leq 55^\circ\text{C}$ )                  | A 415  |
|  | AC-1 ( $\leq 70^\circ\text{C}$ )                  | A 360  |
|  | AC-3 ( $\leq 440\text{V} \leq 55^\circ\text{C}$ ) | A 330  |
|  | AC-4 (400V)                                       | A 160  |
| Rated operational power AC-3 ( $T \leq 55^\circ\text{C}$ )                     | 230V  | kW 90  |
|  | 400V  | kW 160 |
|  | 415V  | kW 160 |
|  | 440V  | kW 160 |
|  | 500V  | kW 200 |
|  | 690V  | kW 250 |
|  | 1000V   | kW 185 |
| Rated operational current AC-3 ( $T \leq 55^\circ\text{C}$ )                   | 230V  | A 330  |
|  | 400V  | A 330  |
|  | 415V  | A 330  |
|  | 440V  | A 330  |
|  | 500V  | A 300  |
|  | 690V  | A 300  |
|  | 1000V   | A 140  |
| Rated operational power AC-1 ( $T \leq 40^\circ\text{C}$ )                     | 230V  | kW 189 |
|  | 400V  | kW 329 |
|  | 500V  | kW 362 |
|  | 690V  | kW 568 |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 1 poles in series | 75V   | A 375  |
|  | 110V  | A 195  |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 2 poles in series | 75V   | A 375  |
|  | 110V  | A 350  |
|  | 220V  | A 300  |
| IEC max current $I_e$ in DC1 with $L/R \leq 1\text{ms}$ with 3 poles in series | 75V   | A 375  |
|  | 110V  | A 350  |

|  |                 |                  |                |
|--|-----------------|------------------|----------------|
|  | 220V            | A                | 350            |
|  | 330V            | A                | 300            |
| IEC max current I <sub>e</sub> in DC1 with L/R ≤ 1ms with 4 poles in series      |                 |                  |                |
|  | 75V             | A                | 375            |
|  | 110V            | A                | 350            |
|  | 220V            | A                | 350            |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 1 poles in series |                 |                  |                |
|  | 75V             | A                | 310            |
|  | 110V            | A                | 170            |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 2 poles in series |                 |                  |                |
|  | 75V             | A                | 310            |
|  | 110V            | A                | 290            |
|  | 220V            | A                | 230            |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 3 poles in series |                 |                  |                |
|  | 75V             | A                | 310            |
|  | 110V            | A                | 310            |
|  | 220V            | A                | 290            |
|  | 330V            | A                | 230            |
| IEC max current I <sub>e</sub> in DC3-DC5 with L/R ≤ 15ms with 4 poles in series |                 |                  |                |
|  | 75V             | A                | 310            |
|  | 110V            | A                | 310            |
|  | 220V            | A                | 310            |
|  | 330V            | A                | 310            |
|  | 460V            | A                | 230            |
| Short-time allowable current for 10s (IEC/EN60947-1)                             |                 | A                | 2640           |
| Protection fuse  |                 |                  |                |
|  | gG (IEC)        | A                | 630            |
|  | aM (IEC)        | A                | 500            |
| Making capacity (RMS value)  |                 | A                | 3300           |
| Breaking capacity at voltage   |                 |                  |                |
|  | 440V            | A                | 2640           |
|  | 500V            | A                | 2240           |
|  | 690V            | A                | 2000           |
| Resistance per pole (average value)  |                 | mΩ               | 0.12           |
| Power dissipation per pole (average value)                                       |                 |                  |                |
|  | I <sub>th</sub> | W                | 30             |
|  | AC-3            | W                | 13             |
| Tightening torque for terminals  |                 |                  |                |
|  | min             | Nm               | 35             |
|  | max             | Nm               | 35             |
|  | min             | I <sub>bin</sub> | 310            |
|  | max             | I <sub>bin</sub> | 310            |
| Tightening torque for coil terminal  |                 |                  |                |
|  | min             | Nm               | 0.8            |
|  | max             | Nm               | 1              |
| Power terminal protection according to IEC/EN 60529                              |                 |                  | IP00           |
| <b>Mechanical features</b>   |                 |                  |                |
| Operating position   |                 |                  |                |
|  | normal          |                  | Vertical plan  |
|  | allowable       |                  | ±30°           |
| Fixing   |                 |                  | Screw          |
| <b>Operations</b>  |                 |                  |                |
| Mechanical life  |                 |                  | cycles 5000000 |

|  |                                 |                 |     |          |            |
|--|---------------------------------|-----------------|-----|----------|------------|
| Electrical life                                    |                                 |                 |     | cycles   | 700000     |
| <b>Safety related data</b>                         |                                 |                 |     |          |            |
| Performance level B10d according to EN/ISO 13489-1 |                                 |                 |     |          |            |
|  |                                 | rated load      |     | cycles   | 700000     |
|  |                                 | mechanical load |     | cycles   | 5000000    |
| EMC compatibility                                  |                                 |                 |     |          | yes        |
| <b>AC coil operating</b>                           |                                 |                 |     |          |            |
| Rated AC voltage at 50/60Hz, 60Hz                  |                                 |                 |     |          |            |
|  |                                 | min             | V   |          | 100        |
|  |                                 | max             | V   |          | 250        |
| AC operating voltage                               |                                 |                 |     |          |            |
|  | of 50/60Hz coil powered at 50Hz |                 |     |          |            |
|  | pick-up                         | min             | %Us |          | 80 Us min  |
|  |                                 | max             | %Us |          | 110 Us max |
|  | drop-out                        | max             | %Us |          | ≤70 Us min |
|  | of 50/60Hz coil powered at 60Hz |                 |     |          |            |
|  | pick-up                         | min             | %Us |          | 80 Us min  |
|  |                                 | max             | %Us |          | 110 Us max |
|  | drop-out                        | max             | %Us |          | ≤70 Us min |
| AC average coil consumption at 20°C                |                                 |                 |     |          |            |
|  | of 50/60Hz coil powered at 50Hz |                 |     |          |            |
|  |                                 | in-rush         | VA  |          | 160...320  |
|  |                                 | holding         | VA  |          | 3.5...8.0  |
|  | of 50/60Hz coil powered at 60Hz |                 |     |          |            |
|  |                                 | in-rush         | VA  |          | 160...320  |
|  |                                 | holding         | VA  |          | 3.5...8.0  |
|  | of 60Hz coil powered at 60Hz    |                 |     |          |            |
|  |                                 | in-rush         | VA  |          | 160...320  |
|  |                                 | holding         | VA  |          | 3.5...8.0  |
| Dissipation at holding ≤20°C 50Hz                  |                                 |                 |     | W        | 3.5...8.0  |
| <b>DC coil operating</b>                           |                                 |                 |     |          |            |
| DC rated control voltage                           |                                 |                 |     |          |            |
|  |                                 | min             | V   |          | 100        |
|  |                                 | max             | V   |          | 250        |
| max  |                                 |                 | V   |          | 250        |
| DC operating voltage                               |                                 |                 |     |          |            |
|  | pick-up                         | min             | %Us |          | 85 Us min  |
|  |                                 | max             | %Us |          | 110 Us max |
|  | drop-out                        | max             | %Us |          | ≤70 Us min |
| Average coil consumption ≤20°C                     |                                 |                 |     |          |            |
|  |                                 | in-rush         | W   |          | 160...230  |
|  |                                 | holding         | W   |          | 3.5...8.0  |
| <b>Max cycles frequency</b>                        |                                 |                 |     |          |            |
| Mechanical operation                               |                                 |                 |     | cycles/h | 1000       |
| <b>Operating times</b>                             |                                 |                 |     |          |            |
| Average time for Us control                        |                                 |                 |     |          |            |
|  | in AC                           |                 |     |          |            |

|            |     |    |     |
|------------|-----|----|-----|
| Closing NO | min | ms | 80  |
|            | max | ms | 120 |
| Opening NO | min | ms | 30  |
|            | max | ms | 75  |

**UL technical data**

|                                   |   |     |
|-----------------------------------|---|-----|
| Rated operational voltage AC (UL) | V | 600 |
|-----------------------------------|---|-----|

Yielded mechanical performance

for three-phase AC motor

|          |    |     |
|----------|----|-----|
| 200/208V | HP | 100 |
| 220/240V | HP | 125 |
| 460/480V | HP | 250 |
| 575/600V | HP | 300 |

**General USE**

Contactor

|            |   |     |
|------------|---|-----|
| AC current | A | 500 |
|------------|---|-----|

Short-circuit protection fuse, 600V

High fault

|                       |    |     |
|-----------------------|----|-----|
| Short circuit current | kA | 100 |
| Fuse rating           | A  | 600 |
| Fuse class            |    | J   |

Standard fault

|                       |    |     |
|-----------------------|----|-----|
| Short circuit current | kA | 18  |
| Fuse rating           | A  | 600 |
| Fuse class            |    | RK5 |

**Ambient conditions**

Temperature

Operating temperature

|     |    |     |
|-----|----|-----|
| min | °C | -40 |
| max | °C | 70  |

Storage temperature

|     |    |     |
|-----|----|-----|
| min | °C | -50 |
| max | °C | 80  |

Max altitude




|   |      |
|---|------|
| m | 3000 |
|---|------|

**Resistance & Protection**


Pollution degree

3

**Dimensions**



**Wiring diagrams**



**Certifications and compliance**

**Compliance**

- CSA C22.2 n° 60947-1
- CSA C22.2 n° 60947-4-1
- IEC/EN/BS 60947-1
- IEC/EN/BS 60947-4-1
- UL 60947-1
- UL 60947-4-1

**Certificates**

cULus

**ETIM classification**

ETIM 8.0

EC000066 -  
Power contactor,  
AC switching