

ML Home

ML HOME 20W E27 827 SLV

0035006

Range features



CE

PRODUCT OVERVIEW

Ordering number	0035006
Technology	Compact Fluorescent
Light colour	827 Homelight
Energy class	A
Average life (Rated) (h)	8000
Lamp shape	Spiral
Lamp finish	Frosted
Dimmable	No
Cap/Base	E27
Type	HOME
EAN code	5410288350066
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	1152
Efficacy (Rated) (lm/w)	58
Watt (Nominal) (W)	20
Equivalent watt (W)	85
Voltage (V)	220-240

ML Home

ML HOME 20W E27 827 SLV

0035006

DATA TABLE

General data

Dry applications use only	Yes
Technology	Compact Fluorescent
Ordering number	0035006
Energy saving lamp	Yes
Average life (Rated) (h)	8000
Energy class	A
Average life (Nominal) (h)	8000
Lamp finish	Frosted
Lamp shape	Spiral
Dimmable	No
Cap/Base	E27
Type	HOME
EAN code	5410288350066
E-number FI	4940273
E-number SE	8357527
Long description	
Product name	ML HOME 20W E27 827 SLV
Lamp mercury content (mg)	<2
Starting time (max) (s)	<1.0
Warm-up time to 60% of full light (max) (s)	<40
Control gear required	NO
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	30000
Special purpose lamp	No
Transformer required	No
Sales pack quantity	10
Optimal operating condition (°C)	25

Optical data

Light colour	827 Homelight
CRI (Ra)	80
Colour temperature (K)	2700
Luminous flux (Rated) (lm)	1152
Lumen maintenance at end of nominal life (%)	65
Luminous flux (Nominal) (lm)	1152

ML Home

ML HOME 20W E27 827 SLV

0035006

Electrical data

kWh per 1000 hours burning time	20
Efficacy (Rated) (lm/w)	58
Watt (Rated) (W)	20
Watt (Nominal) (W)	20
Equivalent watt (W)	85
Voltage (V)	220-240
Lamp power factor	=0.55

Physical data


Weight (kg)	0.08
Lamp Length (mm) - C/L	132.5±3
Max. Lamp Diameter (mm) - D	48±0.5
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	14.50 x 5.00 x 5.00
Outer package dimensions (L x W x H) (cm)	27.00 x 11.00 x 17.00

ML Home

ML HOME 20W E27 827 SLV

0035006

TECHNICAL DRAWINGS



ENERGY LABEL

