


Quick Start Guide

Self-contained, ac-operated sensors






WARNING:

- Do not use this device for personnel protection
- Using this device for personnel protection could result in serious injury or death.
- This device does not include the self-checking redundant circuitry necessary to allow its use in personnel safety applications. A device failure or malfunction can cause either an energized (on) or de-energized (off) output condition.

Models

Model ¹	Sensing Mode		Range	LED	Output
Q403E		Opposed	60 m (200 ft)	Infrared, 950 nm	-
Q40AW3R					LO
Q40RW3R	OPPOSED				DO
Q40AW3LP	POLAR RETRO	Polarized Retro-reflective	6 m (20 ft)	Visible red, 680 nm	LO
Q40RW3LP					DO
Q40AW3FF200	FIXED-FIELD	Fixed Field	200 mm (8 in) cutoff	Infrared, 880 nm	LO
Q40RW3FF200					DO
Q40AW3FF400			400 mm (16 in) cutoff		LO
Q40RW3FF400					DO
Q40AW3FF600			600 mm (24 in) cutoff		LO
Q40RW3FF600					DO

Wiring Diagrams



Original Document 116168 Rev. B

¹ Standard 2 m (6.5 ft) cable models are listed.

[•] To order 9 m (30 ft) cable: add suffix "W/30" (for example, Q403E W/30).

To order 4-pin Euro-style QD models: add suffix "Q1" (for example, Q403EQ1). A model with a QD connector requires a mating cable.

Specifications

Supply Voltage and Current 20 V ac to 250 V ac (50/60 Hz). Average current: 20 mA

Peak current: 200 mA at 20 V ac, 500 mA at 120 V ac, 750 mA at 250 V ac

Supply Protection Circuitry

Protected against transient voltages

Output Configuration

SPST solid-state ac switch; Three-wire hookup; Choose light operate or dark operate

Light Operate: N.O. output conducts when sensor sees its own (or the emitter's)

modulated light

Dark Operate: Output conducts when the sensor sees dark

Output Rating

utput nating 300 mA maximum (continuous) Fixed-Field models: derate 5 mA/°C above +50°C (122°F) Inrush Capability: 1 amp for 20 milliseconds, non-repetitive OFF-state leakage current: < 100 microamps ON-state saturation voltage: 3 V at 300 mA ac; 2 V at 15 mA ac

Required Overcurrent Protection



WARNING: Electrical connections must be made by qualified personnel in accordance with local and national electrical codes and regulations.

Overcurrent protection is required to be provided by end product application per the

Overcurrent protection is required to be provided by end product application per ansupplied table.

Overcurrent protection may be provided with external fusing or via Current Limiting, Class 2 Power Supply.

Supply wiring leads < 24 AWG shall not be spliced.

For additional product support, go to www.bannerengineering.com.

Supply Wiring (AWG)	Required Overcurrent Protection (Amps)		
20	5.0		
22	3.0		
24	2.0		
26	1.0		
28	0.8		
30	0.5		

Output Protection Circuitry
Protected against false pulse on power-up

Output Response Time

Opposed mode: 16 milliseconds ON, 8 milliseconds OFF Other models: 16 milliseconds ON and OFF

Note: 100 ms delay on power-up

Repeatability
Opposed mode: 2 milliseconds
Other modes: 4 milliseconds
Repeatability and response are independent of signal strength

Indicators

Jacators
Two LEDs (Green and Amber)
Green ON steady: power to sensor is ON
Amber ON steady: sensor sees light
Amber flashing: excess gain marginal (1 to 1.5x) in light condition

Construction

PBT polyester housing; polycarbonate (opposed mode) or acrylic lens

Environmental Rating

Leakproof design rated NEMA 6P, DIN 40050 (IP69K per DIN 40050-9)

Connections

2 m (6.5 ft) or 9 m (30 ft) attached cable, or 4-pin Micro-style quick-disconnect fitting **Operating Conditions**

Temperature: -40 °C to +70 °C (-40 °F to +158 °F) 90% at +50 °C maximum relative humidity (non-condensing)

Vibration and Mechanical Shock

All models meet MIL-STD-202F, Method 201A (Vibration: 10 Hz to 60 Hz maximum, 0.06 inch (1.52 mm) double amplitude, 10G acceleration) requirements. Method 213B conditions H&I. Shock: 75G with device operating; 100G for non-operation

Certifications









Dimensions

Cabled Models



QD Models



All measurements are listed in millimeters [inches], unless noted otherwise.

Accessories

Quick-Disconnect (QD) Cables

4-Pin Micro-Style Cordsets—Single Ended						
Model	Length	Style	Dimensions	Pinout (Female)		
MQAC-406	1.83 m (6 ft)		1/2-20 UNF-28 0 14.5 -			
MQAC-415	4.57 m (15 ft)			1 = Red/Black 2 = Red/White 3 = Red 4 = Green		
MQAC-430	9.14 m (30 ft)	Straight				
MQAC-406RA	1.83 m (6 ft)		32 Typ			
MQAC-415RA	4.57 m (15 ft)					
MQAC-430RA	9.14 m (30 ft)	Right-Angle				

Banner Engineering Corp. Limited Warranty

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEALING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp. Any misuse, abuse, or improper application or installation of this product or use of the product for personal protection applications when the product is identified as not intended for such purposes will void the product warranty. Any modifications to this product without prior express approval by Banner Engineering Corp will void the product warranties. All specifications published in this document are subject to change; Banner reserves the right to modify product specifications update documentation at any time. Specifications and product information in English supersede that which is provided in any other language. For the most recent version of any documentation, refer to: www.bannerengineering.com.

For patent information, see www.bannerengineering.com/patents.