

Han® PushPull, type acc. to IEC 61 076-3-118
 Connector, 5-poles, 230/400 V, 16 A

Features

- HARTING PushPull technology
- Compact, space-saving design
- Touch-proof
- Cable side: female
 - crimp termination
 - Han-Quick Lock® termination technology
 Field-assembly without special tools
- 4 times coding without contact loss
- NEW: Larger termination cross section for conductors 0.25 - 1.5 mm²

Technical characteristics

Locking	PushPull technology acc. to IEC 61 076-3-117 variant 14 acc. to IEC 61 076-3-118
Mating face	IP 65 / IP 67
Degree of protection	4 + PE
Number of contacts	16 A 690 V 4 kV 3
Electrical data	0.25 – 2.5 mm ²
acc. to DIN EN 61 984	min. 500
Termination cross section	-40 °C ... +70 °C
Mating cycles	Plastic, black
Temperature range	V0
Housing material	
Flammability acc. to UL 94	


Identification	Part No.	Drawing	Dimensions in mm
----------------	----------	---------	------------------

Connector set, plastic

incl. housing and female insert

with crimp termination
 9 – 13 mm clamp range
 Han® P crimp contacts
 order separately

09 35 231 0423




with Han-Quick Lock® termination
 9 – 13 mm clamp range
 for termination cross section 0.5 - 2.5 mm²

09 35 232 0423

with Han-Quick Lock® termination
 6.5 – 9.5 mm clamp range
 for termination cross section 0.5 - 2.5 mm²
 for termination cross section 0.25 - 1.5 mm²

09 35 232 0421
 09 35 234 0421



Dust protection cover IP 40

09 35 002 5412

Protection cover IP 65 / IP 67

09 35 002 5411

Coding pins

09 35 000 6190