


SYMBOL DEFINITION		TOTAL NO OF INSPECTIONS REQUIRED
□	A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	18
□	LAST NO. USED	12

MISSING SYMBOLS				REVISION HISTORY		AUTH	DR	AP/D	AP/D
DATE	STG	REV	N/P	CHG	ZONE				
21N001	R	01	-	-		CLEARED REV COL & ALL PARTS - REVISED MAT'L SPEC	217409	JAN	RVP RC
19MY03	R	02	-	-		15300017 - OBSOLETE	241251	EOV	EDV RC
29SE04	R	03	-	-		DIM 9 TOLERANCE WAS +.3/- .45, ADDED DIMS 11 AND 12 TO PD AND TBT TO TD	258705	MJM	MJM TM
24MY06	R	04	-	-		15324857 - REVISED TOQ REVISION LEVEL	280148	JS	JS TM
25OC06	R	05	-	-		15324857 - REMOVED DIM #11	286257	JTZ	JVM WTM
17DE06	R	06	-	-		ALL ACTIVE PARTS - REVISED NOTE #2	287948	EES	EES MM



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:  
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
  - MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
  - THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
  - REFERENCE MATING COMPONENTS OR EQUIVALENT:  
CONNECTOR 15300011
  - MAX CABLE DIAMETER THAT WILL FIT PART IS  $\phi$  4.2
  - (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE "PED".

PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	VOL CM <sup>3</sup>	REPLACED BY
15324857	02	AD		M3592001 PA66 IM HS BLK	1.744	-
15300017	04	AA	OBSOLETE	M3592008 PA66 IM HS BLU	1.744	15324857

DELPHI  
DELPHI PACKARD ELECTRIC SYSTEMS  
WARREN, OH

DRAWING NAME		DATE	
TAXI LOCK SECONDARY TPA M/P			
DRAWING NUMBER		DATE	
15324858			
SIZE	SCALE	FRAME NO	SHEET NO
A0	5:1	1	1

DRAWING TYPE		PART DRAWING																					
STYLE		SEE CHART																					
VOLUME (C/P)		DISTR CODE																					
		D																					
UNLESS OTHERWISE SPECIFIED																							
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE IN-SUPPLY DIMENSIONING AND TOLERANCE ADDENDUM-2001. SEPARATE WRITINGS OF FEATURES MAY BE BASED SEPARATELY PER POLICY OF DIVISION REFERENCES.																							
ALL DIMENSIONS ARE IN MILLIMETERS																							
REFERENCE																							
<table border="1" style="font-size: small;"> <tr> <th>DIMENSIONAL RANGE (MM)</th> <th>SHORT ET</th> </tr> <tr> <td>FROM &gt; 0</td> <td>&gt; 30</td> </tr> <tr> <td>TO 20</td> <td>30</td> </tr> <tr> <td></td> <td>70</td> </tr> <tr> <td></td> <td>100</td> </tr> <tr> <td></td> <td>150</td> </tr> <tr> <td></td> <td>200</td> </tr> <tr> <td></td> <td>250</td> </tr> <tr> <td></td> <td>300</td> </tr> <tr> <td></td> <td>400</td> </tr> </table>				DIMENSIONAL RANGE (MM)	SHORT ET	FROM > 0	> 30	TO 20	30		70		100		150		200		250		300		400
DIMENSIONAL RANGE (MM)	SHORT ET																						
FROM > 0	> 30																						
TO 20	30																						
	70																						
	100																						
	150																						
	200																						
	250																						
	300																						
	400																						
DIMENSIONS ENCLOSED IN ( ) INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED																							
DIMENSIONS UNLESS OTHERWISE SPECIFIED																							
<table border="1" style="font-size: x-small;"> <tr> <td>±0.15</td> <td>±0.2</td> <td>±0.3</td> <td>±0.4</td> <td>±0.5</td> <td>±0.6</td> <td>±0.8</td> <td>±1</td> <td>±1.2</td> </tr> <tr> <td colspan="9">ANGULAR TOLERANCE 2°</td> </tr> </table>				±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	ANGULAR TOLERANCE 2°										
±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2															
ANGULAR TOLERANCE 2°																							
THIRD ANGLE PROJECTION		DO NOT SCALE																					
USE MATH DATA																							

Date: 18-Dec-08 Time: 09:45