











JMK4



 T4 BSPP	XXXXX-XX-XX	 PN	 P _{max}	D (mm)	L (mm)	Y (mm)		
							S	SS
1/8	2JMK4	350	500	3,5	16,6	11	●	●
1/4	4JMK4	350	500	4,7	27,8	19	●	●
3/8	6JMK4	350	500	7,9	31,7	22	●	●
1/2	8JMK4	200	260	11,1	37,0	27	●	●
5/8	10JMK4	200	260	14,3	39,0	27	●	●
3/4	12JMK4	200	260	16,7	41,6	33	●	●
1	16JMK4	120	180	22,2	49,7	41	●	●
1 1/4	20JMK4	105	150	28,6	54,4	48	●	●
1 1/2	24JMK4	105	150	33,3	53,7	48	●	●

PNMK4



 T4 BSPP	XXXXX-XX-XX	 PN	 P _{max}	C (mm)	L (mm)		
						S	SS
1/8	2PNMK4	350	500	14	14,3	●	●
1/4	4PNMK4	350	500	19	18,8	●	●
3/8	6PNMK4	350	500	22	20,5	●	●
1/2	8PNMK4	200	260	27	24,0	●	●
5/8	10PNMK4	200	260	30	24,0	●	●
3/4	12PNMK4	200	260	32	26,5	●	●
1	16PNMK4	120	180	41	30,2	●	●
1 1/4	20PNMK4	105	150	50	38,7	●	●
1 1/2	24PNMK4	105	150	55	42,7	●	●
2	32PNMK4	70	90	70	48,2	●	●

Complétez la référence avec la lettre correspondant à la matière choisie:

S = Acier SS = Acier inoxydable

(Exemple: **4JMK4S**)