

# **FEATURES**

- 5 mm high contrast coloured diffused epoxy lens
- Tri-colour options
- Longevity and low
  power consumption
- Bright chrome bezel
- Various voltage ratings

# RS PRO Green Indicator, 12 V dc, 8mm Mounting Hole Size, Solder Tab Termination

RS Stock No.: 211-257



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



### **Product Description**

Brought to you by RS Pro, a range of LED indicators. Each indicator has a compact and robust high quality build, complete with a solder tab termination. The relative ease of the installation process ensures these LED indicators are perfect for your application. With tri-colour options available, the possibilities are endless. Whether the intended application is a signal, warning or purely a display, there are choices to suit all outcomes. All models are highly reliable and excellent quality.

### **General Specifications**

Light Output Colour	Green
Lamp Type	LED
Termination Type	Solder Tab
Туре	Panel Mount
Bezel Style	Prominent
Bezel Colour	Chrome
Intensity	40mcd
Type Of Illumination	Fixed Light
LED Colour	Green
Viewing Angle	30-100°
Life Expectancy	100000hours
Applications	Fixed to PCB circuit boards mounted; Switches; Pushbuttons; Used as vehicle indicators

### **Electrical Specifications**

Voltage Rating	12V dc
Current Rating	20mA
Voltage Tolerance	10%

# Indicators



## **Mechanical Specifications**

Mounting Hole Size	8mm
Length	33.9mm
Torque	20cNm to 25cNm
Lamp Size	5mm

Operation Environment Specifications	
Temperature Rating	-40 to 85°C
Temperature Nating	-40 10 05 0

Approvals	
Compliance/Certifications	EN61340





#### TECHNICAL SPECIFICATIONS

Voltage	Operating Voltage	Operating Current
	(Min to Max)	(Typical All Types)
02 (No Resistor)	1.8 to 3.3VDC	20mA max*
6VDC	5.4 to 6.6VDC	20mA
12VDC	10.8 to 13.2VDC	20mA
24VDC	21.6 to 26.4VDC	20mA
28VDC	25.2 to 30.8VDC	20mA
110VAC	99 to 121VAC	6mA
220VAC	207 to 253VAC	3mA


# Max Reverse Voltage: 5V

Viewing Angle: 30–100° (dependant on model)

Life Expectancy: 100,000 hours

Temperature Range: -40 to +85°C (operating & storage)

Torque: 20 to 25cNm



Standard LED Intensity	Prominent and Recessed	Flush	Forward Voltage
HE Red	80mcd	10mcd	2.0V
Green	60mcd	5mcd	2.2V
Yellow	50mcd	4mcd	2.1V
Blue	540mcd	100mcd	3.3V
White	1000mcd	150mcd	3.3V
Orange	80mcd	200mcd	2.0V
Bi-color (Typical) (Red/Green)	15/15mcd	14/10mcd	2.0V/2.2V
Tri-color (Typical) (Red/Green/Yellow)	60/50/50mcd	15/10/30mcd	2.0V/2.2V/2.1V
Bi-color - The colo	r is changed by reversing the pol	arity of the supply vol	tage.
Tri-color - The indicator h	has red and green LEDs, when bo	oth connected yellow	is produced.
Super Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	17,000mcd	2,000mcd	2.2V
Green	11,000mcd	680mcd	3.5V
Yellow	4,000mcd	350mcd	2.3V
Blue	2,500mcd	250mcd	3.3V
White	4,400mcd	250mcd	3.3V
Orange	2800mcd	300mcd	2.1V
Hyper Bright LED	Prominent and Recessed	Flush	Forward Voltage
HE Red	2,800mcd	800mcd	2.1V
Green	2,200mcd	250mcd	3.2V
Yellow	1,300mcd	250mcd	2.0V
	850mcd	200mcd	2.1V



#### PROMINENT BEZEL

