

standards-based cylinder CRDSNU-B-20-40-PPS-A-MG-A1 Part number: 8073978







Data sheet

Feature	Value
Stroke	40 mm
Piston diameter	20 mm
Based on the standard	ISO 6432
Cushioning	PPS: Self-adjusting pneumatic end-position cushioning
Assembly position	Any
Design structure	Piston
	Piston rod
	Cylinder barrel
Position detection	For proximity sensor
Operating pressure	1 10 bar
Mode of operation	double-acting
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further
	operation)
Corrosion resistance classification CRC	4 - Very high corrosion stress
Food-safe	See Supplementary material information
Ambient temperature	0 80 °C
Theoretical force at 6 bar, return stroke	158 N
Theoretical force at 6 bar, advance stroke	188 N
Moving mass with 0 mm stroke	42.1 g
Additional weight per 10 mm stroke	7.2 g
Basic weight for 0 mm stroke	310 g
Additional mass factor per 10 mm of stroke	3.9 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover	High alloy steel, non-corrosive
Material piston rod	High alloy steel, non-corrosive
Material cylinder barrel	High alloy steel, non-corrosive