




Passive Components > Resistors > Through-Hole Resistors



Resistance Value: 15 Ω

Resistor Type: **Power Resistor**

Element Type: **Ceramic Composition, Wire Wound**

Power Rating: **9 W**

Resistance Class: **Up to 1kΩ**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Ceramic Composition, Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	500 V
Resistance Value	15 Ω
Power Rating	9 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	40 x 8.5 mm
------------------------------	-------------



Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±400 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

EP9WS15RJ

15 ohm, Through-Hole Power Resistor, Ceramic Composition / Wire Wound, 9 W, 5 %, ±400 ppm/°C, Axial-Leaded, Copper Termination, 40 x 8.5 mm, Neohm EP



TE Part # 2176079-5
EP 3W 47R 5%

TE Part # 2176083-1
EP 5W (S) 10R 5%

TE Part # 2176085-7
EP 9W (S) 100R 5%

TE Part # 2176080-2
EP 9W 15R 5%

TE Part # 2176084-7
EP 7W (S) 100R 5%

TE Part # 2176081-7
EP 1W (S) 100R 5%

Also in the Series | **Neohm EP**

Through-Hole Resistors(607)

Customers Also Bought

TE Part #1-1622825-2
RL73K 3A R15 5% 1K Reel

TE Part #4-1415073-1
RT3S4LC4

TE Part #1676221-2
RN 0805 1K0 0.1% 10PPM 1KRL

TE Part #8-1879225-4
CPF 0603 332K 0.1% 25PPM 1K RL

TE Part #3-1416100-0
ST3P2LC4

TE Part #1676282-2
RN 0805 2K0 0.1% 10PPM 1KRL

TE Part #1-1879260-6
RP 2B 3K01 0.1% 15PPM CUT LENGTH

TE Part #1-1879513-8
CRGH1206 1% 15R 0.5W



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2176085-2_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2176085-2_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2176085-2_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Wirewound Anti Surge Resistors - Type EP Series

English