

Eaton 134952

Catalog Number: 134952

Eaton DS7 Soft starter, 41 A, 200 - 480 V AC, 24 V DC, Frame size: FS3, Communication Interfaces: SmartWire-DT

General specifications



Product Name

Eaton DS7 Soft starter

Catalog Number

134952

EAN

4015081317677

Product Length/Depth

156 mm

Product Height

175 mm

Product Width

93 mm

Product Weight

1.8 kg

Certifications

C-Tick
CSA-C22.2 No 0-M91
CE
GB 14048.6
CSA-C22.2 No 14-05
UL
CSA22.2-14
UL 508
CSA
IEC/EN 60947-4-2
UkrSEPRO

Features & Functions

Fault memory

8 Faults

Fitted with:

Internal bypass contacts

Internal bypass

Functions

Single direction

Soft start function

Current limitation, with PKE

Min. ramp time 1 s - fast switching (semiconductor contactor)

Suppression of DC components for motors

Potential isolation between power and control sections

Suppression of closing transients

Interfaces

SmartWire-DT (built-in)

General

Class

Other

Connection to SmartWire-DT

Yes

Degree of protection

IP20

NEMA 1

Frame size

FS3

Mains voltage - max

480 V

Mains voltage - min

200 V

Overvoltage category

II

Pollution degree

2

Product category

SmartWire-DT slave

Radio interference class

Class B (EN 55011)

Suitable for

Branch circuits, (UL/CSA)

Type

Soft starter for three-phase loads

Voltage type

DC

Ambient conditions, mechanical

Mounting position

Vertical

Shock resistance

8 g, 11 ms, Mechanical

Vibration resistance

2M2 to EN 60721-3-2

Climatic environmental conditions

Altitude

Above 1000 m with 1 % derating per 100 m

Max. 2000 m

Ambient operating temperature - min

-5 °C

Ambient operating temperature - max

40 °C

Ambient storage temperature - min

-25 °C

Ambient storage temperature - max

60 °C

Climatic proofing

Damp heat, constant, to IEC 60068-2-3

Damp heat, cyclic, to IEC 60068-2-30

Main conducting paths

Overload cycle

AC-53a: 3 - 5: 75 - 10

Rated operational current (I_e) at AC-53

41 A

Rated operational voltage (U_e) - min

230 V

Rated operational voltage (U_e) - max

480 V

Short-circuit protection rating

3 x 170M3013, Type „2“ coordination (additional with the fuses for coordination type „1“), Main conducting paths

NZMN1-M50/PKZM4-49, Type “1” coordination, Main conducting paths

Supply frequency

50/60 Hz, fLN, Main circuit

Voltage rating - max

480 V

Motor rating

Assigned motor power at 200/208 V, 60 Hz, 3-phase

10 HP

Assigned motor power at 220/230 V, 60 Hz, 3-phase

15 HP

Assigned motor power at 460/480 V, 60 Hz, 3-phase

30 HP

Rated operational power at 220/230 V, 50 Hz

11 kW

Rated operational power at 400 V, 50 Hz

22 kW

Terminal capacities

Terminal capacity (copper band)

2 x 9 x 0.8 mm, Main cables

9 x 9 x 0.8 mm, Main cables

Terminal capacity (flexible with ferrule)

1 x (0.5 - 1.5) mm², Control circuit cables

2 x (0.5 - 0.75) mm², Control circuit cables

Terminal capacity (solid)

2 x (0.5 - 1.0) mm², Control circuit cables

1 x (25 - 70) mm², Main cables

2 x (6 - 25) mm², Main cables

1 x (0.5 - 2.5) mm², Control circuit cables

Terminal capacity (solid/stranded AWG)

2 x (21 - 18), Control circuit cables

1 x (12 - 2/0), Main cables

1 x (21 - 14), Control circuit cables

Terminal capacity (stranded)

2 x (6 - 25) mm², Main cables

1 x (25 - 70) mm², Main cables

2 x (0.5 - 1.0) mm², Control circuit cables

1 x (0.5 - 1.5) mm², Control circuit cables

Tightening torque

6 Nm ($\leq 10 \text{ mm}^2$)

9 Nm ($> 10 \text{ mm}^2$)

0.4 Nm, Screw terminals, Control circuit cables

Control circuit

Current consumption

0,6 A/50 ms, Control circuit, Regulator supply at peak performance (close bypass) at 24 V DC

50 mA, Control circuit, Regulator supply

1.6 mA, Control circuit, Digital inputs, External 24 V

Drop-out time

350 ms, Control circuit, Digital Inputs, DC operated

Drop-out voltage

0 - 3 V, DC operated

Pick-up time

250 ms at DC

Pick-up voltage

17.3 - 27 V DC

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 50 Hz - max

0 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

0 V

Rated control supply voltage (Us) at DC - min

24 V

Rated control supply voltage (Us) at DC - max

24 V

Input/Output

Number of outputs

2 Relay Outputs (TOR, Ready)

Output voltage

250 V AC (relay outputs)

Protection

Finger and back-of-hand proof, Protection against direct contact

Rated control voltage (Uc)

24 V DC

24 V DC (-15 %/+10 %) or via SmartWire-DT

Soft start function

Application

1-phase motors: No

3-phase motors: Yes

Soft starting of three-phase

asynchronous motors

Current limitation

(0 - 8) x I_e, Soft start function

Delay time

Rated operational current (I_e) at AC-11

1 A

0 - 30 s, Soft start function, Ramp times

Ramp/run-up time

1 - 30 s

Start voltage

Max. 100 %, Soft start function, Start voltage = turn-off voltage

Min. 30 %, Soft start function, Start voltage = turn-off voltage

Design verification

Equipment heat dissipation, current-dependent P_{vid}

7 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Rated operational current for specified heat dissipation (I_n)

41 A

Static heat dissipation, non-current-dependent P_{vs}

7 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

Resources

Brochures

[eaton-softstarter-s811-ds7-brochure-br039001en-en-us.pdf](#)

Catalogs

[Product Range Catalog Drives Engineering](#)

Declarations of conformity

[DA-DC-00004193.pdf](#)

[DA-DC-00003978.pdf](#)

Drawings

[eaton-semiconductor-contactors-softstarter-ds7-dimensions-004.eps](#)

[eaton-semiconductor-contactors-softstarter-ds7-3d-drawing-008.eps](#)

eCAD model

[DA-CE-ETN.DS7-34DSX041N0-D](#)

Installation instructions

[IL03902005Z2021_06.pdf](#)

Installation videos

[Soft starter DS7 up to 32 A](#)

Manuals and user guides

[MN03901001Z_EN](#)

[MN05006002Z_EN](#)

mCAD model

[DA-CD-ds7_3_darwin_100316](#)

[DA-CS-ds7_3_darwin_100316](#)

Sales notes

[eaton-rmq-chemical-resistance-flyer-fl047011en-en-us.pdf](#)

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia