

Double screened video cable



Part NO: RGW-1565

Product Code: Double screened video cable

Product Description

Application:

For communication and signal control systems.

Reference Standard

Customer's sample spec.and the general standard

Multi-construction

1

Cable Construction

Conductor	Bare Copper
Construction	0.60±0.01
Stranded Dia	0.60
Insulation	Solid PE
Thickness	1.57
Insulation Dia.(±0.15mm)	3.75
Insulation Color	Nature
Braiding	Tinned Copper
Construction (mm)	T0.15±0.008×16×7
Braiding coverage	94%
Braiding	Tinned Copper
Construction (mm)	T0.15±0.008×16×7
Braiding coverage	92%
Jacket	PVC
Thickness(mm)	>=0.8
Dia.(±0.2mm)	6.40
Jacket Color	Cream(RAL1015)

Marking

Double screened video cable 6.5mm ww/yy +Meter marking

PACKAGING


100M/Reel

RoHS GUIDELINE			
We operate according to the following standards			
Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	/
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	/

Revision History

A0-1

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	65
Min.Insulation DC Resistance at 20°C (M Ω *Km)	>500
Rated Temperature(°C)	-40 to +80
Rated Voltage(V)	30
Capacitance(pF/m)	69
Velocity ratio	65%
Impedance(Ω)	75±3
Attenuation at 20°C (dB/100m) (+/-15%)	
1 MHz	1.1
100 MHz	11
1000 MHz	46

Label on Reel

Product label

Double screened video cable 6.5mm

Cream

100M

RoHS(2002/95/EC) Compliant

WW/YY

RS label

7492526

100M

Made in China



Date: 2011-09-13

Page: 1 / 1