KEMET Part Number: C0402C221J5GACTU

(C0402C221J5GAC7867)



SMD Comm C0G, Ceramic, 220 pF, 5%, 50 VDC, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0402



Dimensions	
L	1mm +/-0.05mm
W	0.5mm +/-0.05mm
Т	0.5mm +/-0.05mm
S	0.3mm MIN
В	0.3mm +/-0.1mm

Packaging Specifications		
Packaging:	T&R, 180mm, Paper Tape	
Packaging Quantity:	10000	

General Information	
Supplier:	KEMET
Series:	SMD Comm C0G
Style:	SMD Chip
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Class I
Features:	Ultra-Stable, Low Loss, Class I
RoHS:	Yes
Termination:	Tin
Marking:	No
Miscellaneous:	Note: KEMET 50V rated parts may be operated at 63 Volts
Chip Size:	0402

Specifications		
Capacitance:	220 pF	
Capacitance Tolerance:	5%	
Voltage DC:	50 VDC	
Dielectric Withstanding Voltage:	125 VDC	
Temperature Range:	-55/+125C	
Temperature Coefficient:	COG	
Dissipation Factor:	0.10% 1MHz 25C	
Aging Rate:	0% Loss/Decade Hour	
Insulation Resistance:	100 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

