

FV-300



Model No.	Packing List	
FV-300		● Unit ● Instruction manual (Japanese only)

Model No.	FV-300
Power consumption	1000 W
Max. temperature	440°C (40 to 440°C continuously variable)
Air velocity	LOW : 230 m/min. HIGH : 460 m/min.
Air flow	LOW : 0.1 m ³ /min. HIGH : 0.2 m ³ /min.
Dimensions	272 (W) × 245 (H) × 81 (D) mm
Weight	0.62 kg

*Dimensions and weight are measured without cord.

*Maximum temperature is approximate one which measured at the point 10mm from the pipe. Measuring condition is the same for low or high air-flow.

シュリンク包装・工業用ドライヤー/工業用ドライヤー

FV-300



品番	セット内容
FV300-81	● 本体 ● 取扱説明書

品番	FV300-81
電源	AC100V 50/60Hz
消費電力	1000W
プラグ形状	平型プラグ
最高温度	440℃ (40～440℃連続可変)
風速	LOW : 230m/min. HIGH : 460m/min.
風量	LOW : 0.1m ³ /min. HIGH : 0.2m ³ /min.
外形寸法	272(W)×245(H)×81(D)mm
重量	0.62kg

※外形寸法と重量はコードを除きます。

※最高温度は吹出し口から10mmで測定。風量 LOW またはHIGH 時でも同じ。