

Traditional external micrometer with pearl-chrome plated frame.



Features

- Tungsten carbide measuring faces
- Pearl-chrome plated frame with insulation pads
- Standard, or vernier sleeve for higher resolution
- Speeder type ratchet
- Locking lever
- Adjusting key
- 5mm spindle diameter
- Tapered bow frame
- Standards: BS870, DIN 863/1, ISO361
- Supplied in a plastic pocket case

Specification

Code No	Range (mm)	Resolution (mm)	Code No	Range (inch)	Resolution (inch)
1961M	0-25	0.01	1961	0-1	0.001
1961MB	0-25	0.002	1961B	0-1	0.0001

Accuracy

Micrometer Range Max Size up to	Measuring Faces Flatness	Screw Pitch Parallelism	Accuracy
25mm	0.001mm	0.003mm	0.003mm
1"	0.00005"	0.0001"	0.0001"