



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **3.31 – 5.26 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	22.1 mm[.87 in]
Compatible Insulation Diameter Range	3.81 – 5.08 mm[.15 – .2 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	3.31 – 5.26 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Quantity	1500
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



KIT

REPRESENTATION ONLY


TE Part # 7-2151724-7
[OCEAN_2.0_SPARE_PART_KIT-140F220F](#)



TE Part # 2305570-1
[Strip Terminal Cutter-Side Feed-No Crimp](#)



TE Part # 171809-2
[POSITIVE LOCK \(PL\) HOUSING](#)



TE Part # 171810-2
[POSITIVE LOCK HOUSING RECEPTACLE](#)



TE Part # 2151724-2
[OCEAN_2.0_Applicator-S-140F220F-RSA](#)




TE Part # 171809-1
[POSITIVE LOCK \(PL\) HOUSING](#)

Also in the Series | Positive Lock 250



[Automotive Terminals\(1\)](#)



[Crimp Terminal Housings\(177\)](#)



[Insertion & Extraction Tools\(3\)](#)



[Insulation Boots & Sleeves\(5\)](#)



Quick Disconnects(173)

Customers Also Bought



TE Part #1-154719-0
PL 250 REC HSG 1P NYLON NAT




TE Part #154718-3
PL 250 REC 0.7-2.0 MM2 0.406 TPBR



TE Part #4454613006
55A0111-8-9



TE Part #1-172132-1
FF 250 PLUG HSG 3P NYLON NAT



TE Part #170340-1
FF 250 TAB 20-14AWG BR WITHOUT LATCH



TE Part #170089-2
FF 250 REC 14-12AWG TPBR



TE Part #160300
PLASTI-GRIP 12-10 RING M10



TE Part #170342-2
250 FASTON,REC.,20-14 AWG,TPBR



TE Part #53427-1
TERMINAL,PIDG PVF2 R 12-10



TE Part #1-172130-1
250 FASTON HSG,PLUG 2P NATURAL

Documents

Product Drawings
POSITIVE LOCK RECP

Japanese

CAD Files
Customer View Model
ENG_CVM_CVM_170234-1_K.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_170234-1_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_170234-1_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of Positive Lock Receptacle Contact

English

Application Specification

English

Agency Approvals

UL

English