



Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 40

Primary Product Color: Black

Protection & Strain Relief Accessory Type: Cover Housing

Primary Product Material: PBT GF15

Cable Exit Angle: 90 °

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover Housing

Configuration Features

Number of Positions	40
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF15
Cable Exit Angle	90 °

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	120 °C[248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #368388-1
MQS RETAINER HSG FOR 40P

TE Part #368389-1
COVER HSG FOR 81P()

TE Part #CAT-T4827-CH8172
Timer Connector Housing

TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB

TE Part #5-968221-1
MQS0,63 Sn rec CB unseal. 0,5-0,75

TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

TE Part #1-368376-1
81P REC HSG ASSY(BLK-B)

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_368401-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_368401-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_368401-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

MQS CLEAN BODY PLUG ASSY 81P & 40P

Japanese

Product Specification

Japanese