




Terminals & Splices > Foil Terminals



Foil Terminal Type: **Strip Tap**
Foil Terminal Body Type: **Type 5**
Accepts Foil Thickness (Max): **.76 mm [.03 in]**
Terminal Plating Material: **Tin**
Packaging Method: **Box**

Features

Body Features

Foil Terminal Body Type	Type 5
-------------------------	--------

Contact Features

Foil Terminal Type	Strip Tap
Terminal Plating Material	Tin

Termination Features

Accepts Foil Thickness (Max)	.76 mm[.03 in]
------------------------------	----------------

Dimensions

Wire Size	1.25 – 2 mm ²
-----------	--------------------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	2000
Packaging Method	Box



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | [TERMI-FOIL](#)



Foil Terminals(23)

Customers Also Bought



TE Part #NB-PTCO-002
Pt100, 2.0x2.3, Class B, PTFC101B1G0



TE Part #640581-1
06P UMNL PLUG HSG



TE Part #1-480702-0
04P UMNL PLUG HSG NATL



TE Part #3-1622796-0
YR1 0.1% 4K75



TE Part #329860
TERMINAL,TERMI-FOIL 16-14




TE Part #794276-1
06P UMNL WIRE SEAL




TE Part #794275-1
06P UMNL INTERFACE SEAL



TE Part #350809-1
05P UMNL PLUG HSG



TE Part #GA100K6MBD425
MBD9-MBD



TE Part #GA50K6A1271-6
DISC- - BTC

Documents

Product Drawings

TERMINAL,TERMI-FOIL 16-14

English

CAD Files

Customer View Model

ENG_CVM_53645-2_O.3d_igs.zip

English

Customer View Model

53645-2

Strip Tap, Type 5, Tin Plating, Box, 16 – 14 AWG, 1.25 – 2 mm² Wire, TERMI-FOIL, Foil
Terminals



[ENG_CVM_53645-2_O.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_53645-2_O.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.