



- OPERATING TEMP. RANGE : -40°C TO +150°C WETSIDE.
- OPERATING PRESSURE : 100 BAR BETWEEN -40°C TO +50°C AND DERATE LINEARLY TO 85 BAR AT +150°C.
- OPERATING VOLTAGE : 20 - 264Vac 50/60Hz. 20 - 60Vdc. DIRECT LOAD SWITCHING (2 WIRE).
- LOAD CURRENT : 20 - 500mA
- EARTH : SENSOR BODY MUST BE EARTHED.
- TERMINAL BLOCK : SCREW CLAMP TO TAKE 2.5mm MAXIMUM WIRE SIZE.
- MATERIALS : BODY AND LID - PA66 30% GF.  
LENS - PMMA  
SENSOR BODY - 316 STAINLESS STEEL.
- WEATHER PROOFING : IP66/IP67 TO BS EN 60529.

ISSUE TO CUSTOMER:	TAG No:
CUSTOMER:	
CUSTOMER ORDER No:	
MOOREY ORDER No:	
CERTIFIED	DATE

NOT TO SCALE			
CAD PRODUCED A3 DRAWING			
ALL DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE STATED			
DRAWN	2/12/02	HB	
ORG. ISSUE	DATE	CHECKED	
1	2/12/02	JPA	

**SOLARTRON MOOREY**

TITLE  
SQUING 2 1"BSPT (R)  
DIRECT LOAD SWITCHING

ORG. NO.  
CD-419-4755