

SAC-14P- 5,0-PUR/M16FRX - Master cable



1260742

<https://www.phoenixcontact.com/in/products/1260742>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Master cable, application: Sensor/actuator box, number of slots: 10, number of positions: 14, slot assignment: single, status display: No; master cable connection: M16 plug connection, PUR/PVC, cable length: 5 m, shielding: no, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1260742
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	*****
Product key	ABRDAB
GTIN	4063151413934
Weight per piece (including packing)	665 g
Weight per piece (excluding packing)	608.8 g
Customs tariff number	85444290
Country of origin	DE

SAC-14P- 5,0-PUR/M16FRX - Master cable



1260742

<https://www.phoenixcontact.com/in/products/1260742>

Technical data

Product properties

Product type	Master cable, assembled
Application	Sensor/actuator box
Number of positions	14
Number of slots	10

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC

Connection data

Connection method	Fixed connection
-------------------	------------------

Signaling

Status display present	No
------------------------	----


Material specifications

Material Housing	PUR
Material Threaded sleeve	Cu alloy
Seal material	NBR
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of contact, master cable side	CU alloy
Material of the contact carrier on the master cable side	TPU
Material of contact surface, master cable side	gold-plated

Cable/line

Cable length	5 m
--------------	-----

PUR/PVC black [PUR]

Dimensional drawing	
Cable weight	111.1 kg/km
UL AWM Style	20549
Number of positions	12

SAC-14P- 5,0-PUR/M16FRX - Master cable



1260742

<https://www.phoenixcontact.com/in/products/1260742>

Shielded	no
Cable type	PUR/PVC black [PUR]
Conductor structure signal line	19x 0.15 mm
AWG signal line	22
Conductor structure, voltage supply	42x 0.15 mm
AWG power supply	18
Conductor cross section	10x 0.34 mm ² (Signal line)
	2x 0.75 mm ² (power line)
Wire diameter incl. insulation	1.3 mm ±0.1 mm (Signal line)
	1.8 mm ±0.1 mm (power line)
External cable diameter	8.60 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, white, green, yellow, gray, pink, red, black, violet, white/pink, pink/brown
Inner sheath thickness	≥ 0.15 mm
Thickness, outer sheath	≥ 0.38 mm
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V
Test voltage	2000 V
Minimum bending radius, fixed installation	7.5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	65 mm
Smallest bending radius, movable installation	86 mm
Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 86 mm, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)
	80 °C (in acc. with UL)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-40 °C ... 90 °C (cable, fixed installation)

SAC-14P- 5,0-PUR/M16FRX - Master cable




1260742

<https://www.phoenixcontact.com/in/products/1260742>

Drawings

Circuit diagram



Contact assignment of the M16 socket

SAC-14P- 5,0-PUR/M16FRX - Master cable



1260742

<https://www.phoenixcontact.com/in/products/1260742>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1260742>



EAC

Approval ID: 19060508

SAC-14P- 5,0-PUR/M16FRX - Master cable



1260742

<https://www.phoenixcontact.com/in/products/1260742>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

SAC-14P- 5,0-PUR/M16FRX - Master cable



1260742

<https://www.phoenixcontact.com/in/products/1260742>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in