# **SIEMENS**

Product data sheet 3RV1321-4DC10



CIRCUIT-BREAKER N-RELEASE 325 A, SIZE S0, STARTER PROTECTION, 50 KA SCREW CONNECTION STANDARD BREAKING CAPACITY

General technical data:		
product brand name		SIRIUS
product designation		circuit breaker
Size of the circuit-breaker		S0
Degree of pollution		3
Installation altitude / at a height over sea level / maximum	m	2,000
Protection class IP / on the front		IP20
Ambient temperature		
during storage	°C	-50 +80
during operating	°C	-20 +70
during transport	°C	8050
Resistance against shock		25g / 11 ms
Insulation voltage / rated value	V	690
Impulse voltage resistance / rated value	V	6,000
Active power loss / total / typical	W	8
Item designation		
<ul> <li>according to DIN 40719 extendable after IEC 204-2 / according to IEC 750</li> </ul>		Q
according to DIN EN 61346-2		Q
Mechanical operating cycles as operating time / of the main contacts / typical		100,000

Type of the driving mechanism / motor drive		No
Design of the operating mechanism		selector switch
Product function		
overload protection		No
phase disturbance recognition		No
Product component		
auxiliary switch		No
undervoltage release mechanism		No
• trip indicator		No
Product extension / optional / motor drive		No
Main circuit:		
Number of poles / for main current circuit		3
type of voltage		AC/DC
Operating voltage / at AC-3 / rated value / maximum	V	690
Operating current / at AC-3 / at 400 V / rated value	Α	25
Service power / at AC-3		
• at 400 V / rated value	kW	11
Frequency of operation / at AC-3 / according to IEC 60947-6-2 / maximum	1/h	15
Arrangement of electrical connectors / for main current circuit		front side
Adjustable response current		
of the non-delayed short-circuit release	Α	325 325
Continuous current / rated value	Α	25
Product extension / auxiliary switch		Yes
Auxiliary circuit:		
Number of NC contacts / for auxiliary contacts / instantaneous switching		0
Number of NO contacts / for auxiliary contacts / instantaneous switching		0
Number of change-over switches / for auxiliary contacts		0
Inputs/ Outputs:		
Number of digital inputs		0
Short-circuit:		
Breaking capacity limit short-circuit current (lcu)		
• at 400 V / rated value	kA	50
• at 500 V / rated value	kA	10
• at 690 V / rated value	kA	4
Design of the electrical connection / for auxiliary and control current circuit		screw-type terminals

Design of the overcurrent release and short-circuit release		magnetic
Installation/mounting/dimensions:		
Built in orientation		any
Type of mounting		screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022
Width	mm	45
Height	mm	97
Depth	mm	96
Distance, to be maintained, to the ranks assembly		
• backwards	mm	0
• sidewards	mm	0
Product function / removable terminal for auxiliary and control circuit		No
Connections:		
Design of the electrical connection		
for main current circuit		screw-type terminals
Type of the connectable conductor cross-section		
• for main contacts		
• solid		2x (1 2.5 mm²), 2x (2.5 6 mm²)
• stranded		2x (1 2.5 mm²), 2x (2.5 6 mm²)
• finely stranded		
with conductor end processing		2x (1 2.5 mm²), 2x (2.5 6 mm²)
for AWG conductors / for main contacts		2x (14 10)
Conductor cross section that can be connected / for main contacts		
• solid	mm²	1 6
• stranded	mm²	1 6
• stranded wire		
with conductor end processing	mm²	1 6
AWG number / as coded connectable conductor cross-section		
• for main contacts		14 10

## Certificates/approvals:

## **General Product Approval**

**Test Certificates** 





**KETI** 

**ROSTEST** 



Manufacturer

## **Shipping Approval**









other

Manufacturer

other

## Safety:

Protection against electrical shock

finger-safe

## **Further information:**

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/industrial-controls/catalogs

#### Industry Mall (Online ordering system)

http://www.siemens.com/industrial-controls/mall

#### **CAx-Online-Generator**


http://www.siemens.com/cax


#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

http://support.automation.siemens.com/WW/view/en/3RV1321-4DC10/all


## Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax\_en.aspx?mlfb=3RV1321-4DC10









last change: Feb 6, 2012