



E2E-X22C130 2M

Proximity sensor, inductive, nickel-brass, short body, M30, shielded, 22 mm, DC, 3-wire, NPN NO, 2 m cable

Specifications

Size	M30
Mounting type	Quasi-flush
Sensing distance	22 mm
Overall length of sensor	60.3 mm
Thread length	38 mm
Material housing	Brass, nickel plated
Output type	NPN
Operation mode	NO
Connection method	Cable
Cable specifications	PVC (oil-resistant)
Cable length	2 m
IO-Link function	×
IO-Link baud rate	Not Applicable
Degree of protection (IP)	IP67/IP67G/IP69K

Downloads

CAD Library



E2E NEXT Datasheet

EN PDF 40 MB



E2E(Q)- XB_XC_premium_model Instruction Sheet

EN PDF 3.66 MB



IO-Link Series Brochure

EN PDF 7.95 MB

