

# Belt Sander XGT®, BS001G

120 - 470 m/min, 76 x 533 mm

Model BS001G is a 3" Belt sander powered by a 40Vmax XGT Li-Ion battery

Main Feature and Benefits: Automatic belt position adjustment, Dust bag with anti-drop feature, Angle adjustable front handle, Angle adjustable LED job light, The tool can be installed upside down for stationary use, Compatible with AWS (Auto-start wireless system).



## Technical specifications

|                                                       |                        |
|-------------------------------------------------------|------------------------|
| Nominal Battery Voltage                               | 40 V                   |
| Belt Speed                                            | 120 - 470 m/min        |
| AWS ready                                             | ✓                      |
| Belt Size                                             | 76 x 533 mm            |
| Sound Pressure Level (L <sub>pA</sub> )               | 87 dB(A)               |
| Product net weight                                    | 3,8 kg                 |
| Noise Uncertainty (K Factor)                          | 3 dB(A)                |
| Tool weight with battery                              | 4,5 - 5,1 kg           |
| Product Dimensions (L x W x H):                       | 440 x 148 x 165 mm     |
| Vibration Level, Sanding Metal Plate                  | ≤ 2,5 m/s <sup>2</sup> |
| Vibration Uncertainty (K Factor), Sanding Metal Plate | 1,5 m/s <sup>2</sup>   |
| Vacuum cleaner connection Ø in / out                  | 22 mm                  |
| Brushless Motor                                       | ✓                      |

## User benefits

- Lock-on feature for continuous operation
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Adjustable handle

Link to product - [www.makita.uk.com](http://www.makita.uk.com)



# Related products

Optional AC

1915E3-1

Angled Guide Rule for Belt Sander



192694-6

2 Piece Clamp Set



193070-7

Sanding Shoe Assembly



193197-3

Carbon Plate



193199-9

Cork Rubber Plate



821552-6

Makpac case (4)



836103-2

Inner Tray



Other

User manual

Parts drawing