

DMUK 200

Torque wrench DREMASTER® UK

20-300 Nm / 15-220 lbf·ft

Code	ETIM
2641313	EC002132
EAN	UNSPSC
4002805931455	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



Article description

- Use:
- Controlled screw tightening in the range of 40 - 200 Nm / 30 - 150 lbf·ft
- Adjustable, releasing and sturdy tubular torque wrench with integrated ratchet and with square drive for industry and the trades
- Features:
- Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- For controlled clockwise tightening
- With 1/2" reversible ratchet
- Sturdy, varnished tubular steel construction, with zinc-plated ratchet head and top-grade plastic parts
- Ergonomically shaped plastic handgrip with calibration aid
- Change-over between Nm main scale and lbf·ft ancillary scale to avoid reading errors when setting the torque wanted
- With micrometre scale for main Nm scale for setting interim values
- Release system triggers a tactile and audible signal
- Ergonomic system for torque adjustment with reference symbol
- Provision for rapid setting with hexagon allen key, not included
- Secured adjusting/setting system

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [N·m]	40 Nm - 200 Nm
Net weight [kg]	1,4 kg	Torque range (min./max.) [lbf·ft]	30 lbf·ft - 150 lbf·ft
Total length [mm]	530 mm	Trigger mechanism	Short path triggering
Total width [mm]	44 mm	Precision +/-	+/- 3 %
Total height [mm]	44 mm	Direction of tightening	Right
Material	Tubular steel construction, top-grade plastic parts	Fixed setting	no
Drive connector square (male)	1/2"	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	12,5 mm	Head height l [mm]	22 mm
Return angle	7,5°	Width of head l [mm]	42,5 mm
Number of teeth	48	Calibration length	435,2 mm
Drive type/drive	Reversible ratchet	Graduation [lbf·ft]	10 lbf·ft
Torque (min.) [N·m]	40 Nm	Graduation [n·m]	10 Nm
Torque (max.) [N·m]	200 Nm	vernier Nm	1 Nm
Torque (min.) [lbf·ft]	30 lbf·ft	Distance housing - square drive	21,25 mm
Torque (max.) [lbf·ft]	150 lbf·ft	Storage/Content	Plastic box