




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 20
Primary Product Color: Black
Protection & Strain Relief Accessory Type: Cover
Primary Product Material: PBT GF15
Cable Exit Angle: 90°

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover

Configuration Features

Number of Positions	20
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF15
Cable Exit Angle	90°

Mechanical Attachment

Strain Relief	Without
---------------	---------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Carton
------------------	--------



Other

Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1534102-1
20POS MQS REC



TE Part # 966871-1
MOD2 ST-WANNE 2X10P

Customers Also Bought






TE Part #CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part #1-1718346-3
3POS MQS REC COD A



TE Part #965786-1
ABDECKKAPPE 180GRD



TE Part #5-962885-1
MQS0,63 Sn rec LL EDS 0,2-0,35



TE Part #1823111-1
SINGLE WIRE SEAL,FOR WIRE 2.5
SQMM,BN

Documents

Product Drawings
MQS ABDECKKAPP2X10P
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-1534099-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1-1534099-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-1534099-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English