

AMP Signal Double Lock


TE Internal #: 1376478-2

PCB Mount Header, Vertical, Wire-to-Board, 2 Position, 2.5 mm [.098 in] Centerline, Fully Shrouded, Tin (Sn), AMP Signal Double Lock

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Number of Rows: **1**

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VDC
-------------------	--------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features

Contact Underplating Material	Copper
Contact Underplating Material Thickness	.5 – 1.2 µm[19.68 – 47.24 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.8 µm[31.49 µin]
Mating Square Post Dimension	.5 mm[.02 in]
PCB Contact Termination Area Plating Material Thickness	.8 – 1.6 µm[31.49 – 62.99 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	4.35 mm[.17 in]
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Pin
Contact Current Rating (Max)	2.5 A

Termination Features

Termination Post & Tail Length	3.2 mm[.126 in]
Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mating Retention Type	Latch
Mating Retention	With
Mating Alignment Type	Polarization
PCB Mount Retention Type	Kinked
PCB Mount Alignment Type	Boss
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Housing Material	Nylon 66 GF
------------------	-------------



Centerline (Pitch)	2.5 mm[.098 in]
--------------------	-----------------

Dimensions

Connector Width	8.2 mm[.32 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	8.8 mm[.34 in]
Connector Length	7.5 mm[.29 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	400
Packaging Method	Bag, Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1376477-2
2.5MM PITCH SIGNAL MATE CONN

TE Part # CAT-SI261-H342
STD Temp Signal Double Lock Header

Also in the Series | AMP Signal Double Lock

Connector Caps & Covers(1)

Connector Contacts(14)

Connector Hardware(19)

Connector Seals & Cavity Plugs(10)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(146)

Rectangular Power Connectors(46)

Wire-to-Board Headers & Receptacles (146)

Customers Also Bought


TE Part #2-2360540-4
SGI 1.25 HDR, 4P, VT, Key B, Black

TE Part #1565081-1
GRACE INERTIA CONNECTOR 3.5 2P

TE Part #1565085-1
GRACE INERTIA CONNECTOR 3.5 2P

TE Part #7-1747072-2
GRACE INERTIA CONN 2.5 ON TAPE HDR 2P BL





TE Part #1744103-1
3.96 EPHDR ASSY 3P OMIT #2 PIN



TE Part #2360540-4
SGI 1.25 HDR, 4P, VT, Key A, Natural



TE Part #1747049-1
GRACE INERTIA CONNECTOR 6.5 3POS HEADER



TE Part #2-1747052-3
GIC 7.92MM CONN HDR ASS'Y 2POS BLUE



TE Part #5-1376492-2
2.5 SMC HDR 2P WHITE TAPE

TE Part #2-1744105-4
EP HDR ASSY 5P omit 2&4,yellow

Documents

Product Drawings

2.5 SMC HDR 2POS WHITE (LP)

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1376478-2_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_1376478-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_1376478-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English