

D-Sub 09-pole MinD solder cup female nut



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 67 009 1715 |
| Specification | D-Sub 09-pole MinD solder cup female nut |
| HARTING eCatalogue | https://harting.com/09670091715 |

Identification

| | |
|----------------------------|--------------------|
| Category | Connectors |
| Series | D-Sub |
| Identification | Standard |
| Element | Connector |
| Description of the contact | Turned Straight |

Version

| | |
|--------------------|--------------------------------|
| Termination method | Solder cup termination |
| Gender | Female |
| Size | D-Sub 1 |
| Connection type | PCB to cable Cable to cable |
| Number of contacts | 9 |
| Locking type | Fixing flange with thread M3 |

Technical characteristics

| | |
|-------------------------------|---------------------|
| Conductor cross-section | 0.5 mm ² |
| Conductor cross-section [AWG] | AWG 20 |
| Rated current | 7.5 A |
| Clearance distance | ≥1 mm |
| Creepage distance | ≥1 mm |
| Insulation resistance | >10 ¹⁰ Ω |
| Contact resistance | ≤10 mΩ |



Pushing Performance
 Since 1945

Technical characteristics

| | |
|----------------------------------|-----------------------------|
| Stripping length | 2.5 ... 3 mm |
| Tightening torque | ≤0.6 Nm Female screw lock |
| Limiting temperature | -55 ... +125 °C |
| Insertion force | ≤30 N |
| Withdrawal force | ≥3.3 N ≤20 N |
| Performance level | 2 acc. to CECC 75301-802 |
| Mating cycles | ≥250 |
| Test voltage U _{r.m.s.} | 1 kV |
| Hot plugging | No |

Material properties

| | |
|---|---|
| Material (insert) | Thermoplastic resin, glass-fibre filled (PBTP) Shell: steel, tin plated |
| Colour (insert) | White |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Noble metal over Ni Mating side Sn over Ni Termination side |
| Material flammability class acc. to UL 94 | V-0 |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | ecef7555-f643-4ceb-a337-fc54762297f1 |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead Nickel |



Pushing Performance
Since 1945

Specifications and approvals

| | |
|----------------|-----------------------|
| Specifications | DIN 41652 |
| UL / CSA | UL 1977 ECBT2.E102079 |

Commercial data

| | |
|--------------------------------|------------------------|
| Packaging size | 100 |
| Net weight | 1 kg |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| GTIN | 5713140217348 |
| ETIM | EC001136 |
| eCl@ss | 27440214 D-Sub coupler |