



■ Features :

- Universal AC input / Full range (up to 305VAC)
- Built-in active PFC function
- Protections: Short circuit / Over current / Over voltage / Over temperature
- · OCP point adjustable through output cable or internal potentiometer
- IP67/IP65 design for indoor or outdoor installations
- Suitable for dry / damp / wet locations
- 5 years warranty, Tc70°C 40000hrs

IP65 IP67 🕞



HBG-240-60 A

Blank: IP67 rated. Cable for I/O connection.

A: IP65 rated. Output constant current level can be adjusted through internal potentiometer.

B: IP67 rated, output constant current lever can be adjusted through output cable with 1-10V,PWM signal and Resistance

SPECIFICATION


MODEL		HBG-240-24	HBG-240-36	HBG-240-48	HBG-240-60								
	DC VOLTAGE	24V	36V	48V	60V								
ОИТРИТ	CONSTANT CURRENT REGION Note.4		21.6 ~ 36V	28.8 ~ 48V	36 ~ 60V								
	RATED CURRENT	10A	6.7A	5A	4.0A								
	RATED POWER	240W	240W	240W	240W								
	RIPPLE & NOISE (max.) Note.2		250mVp-p	250mVp-p	350mVp-p								
	()	Can be adjusted by internal pote			оос р р								
	CURRENT ADJ. RANGE	6~10A 4.0~6.7A 3~5A 2.4~4.0A											
	VOLTAGE TOLERANCE Note.3			15 55.5									
	LINE REGULATION	±0.5%											
		±0.5%											
		2500ms,120ms at full load 230	IVAC /115VAC										
	HOLD UP TIME (Typ.)	15ms at full load 230VAC /115	VAC										
	,	90 ~ 305VAC 127 ~ 431VD0	0 ~ 305VAC 127 ~ 431VDC										
	FREQUENCY RANGE	47 ~ 63Hz	-										
	POWER FACTOR (Typ.)	PF>0.98/115VAC, PF>0.95/230VAC, PF>0.93/277VAC at full load (Please refer to "Power Factor Characteristic" curve)											
	EFFICIENCY (Typ.)	92.5%	93.5%										
INPUT	AC CURRENT (Typ.)	92.5% 92.5% 93% 93.5% 2.5A / 115VAC 1.3A / 230VAC 1.2A / 277VAC											
	MAX.LED DRIVE NUMBER ON MCB C TYPE 16A	8units@230VAC											
	INRUSH CURRENT (Typ.)	COLD START 75A(twidth=680µs measured at 50% Ipeak) at 230VAC											
	LEAKAGE CURRENT	<0.75mA / 277VAC											
	OVER CURRENT Note.4	95 ~ 108%											
		Protection type: Constant current limiting, recovers automatically after fault condition is removed											
	SHORT CIRCUIT	Hiccup mode, recovers automatically after fault condition is removed.											
PROTECTION		27 ~ 34V	43 ~ 52V	52 ~ 63V	62 ~ 85V								
	OVER VOLTAGE	Protection type : Shut down and latch off o/p voltage, re-power on to recover											
		95°C±5°C (TSW1)											
	OVER TEMPERATURE	Protection type : Shut down o/p voltage, recovers automatically after temperature goes down											
	WORKING TEMP.	-40 ~ +70°C (Refer to "Derating	Curve")										
	WORKING HUMIDITY	20 ~ 95% RH non-condensing											
ENVIRONMENT	STORAGE TEMP., HUMIDITY	-40 ~ +80°C, 10 ~ 95% RH											
	TEMP. COEFFICIENT	±0.03%/°C (0 ~ 50°C)											
	VIBRATION	10 ~ 500Hz, 5G 12min./1cycle, period for 72min. each along X, Y, Z axes											
	SAFETY STANDARDS	Design refer to EN61347-2,13,UL8750											
SAFETY &	WITHSTAND VOLTAGE	I/P-O/P:3.75KVAC I/P-FG:2.	0KVAC O/P-FG:0.5KVA	AC .									
EMC	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M	Ohms / 500VDC / 25°C/ 7	0% RH									
	EMC EMISSION	Compliance to EN55015, EN550	161000-3-3										
	EMC IMMUNITY	Compliance to EN61000-4-2,3,4,5,6,8,11, EN61547, light industry level (surge 4KV), criteria A											
	MTBF	190.7Khrs min. MIL-HDBK-217F (25°C)											
OTHERS	DIMENSION	Refer to mechanical specification											
	PACKING	2.1Kg; 8pcs/17.8Kg/1.5CUFT											
NOTE	 All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1uf & 47uf parallel capacitor. Tolerance: includes set up tolerance, line regulation and load regulation. Constant current operation region is within 60% ~100% rated output voltage. This is the suitable operation region for LED related applications, but please reconfirm special electrical requirements for some specific system design. Derating may be needed under low input voltages. Please check the static characteristics for more details. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again. Length of set up time is measured at first cold start. Turning ON/OFF the power supply may lead to increase of the set up time. 												



■ Mechanical Specification


Case No. 213 Unit:mm

Blank:(HBG-240)




XIP67 rated. Cable for I/O connection.

A type:(HBG-240-_A)



XIP65 rated. Output constant current level can be adjusted through internal potentiometer.


B type:(HBG-240-_B)



 \times IP67 rated. output constant current lever can be adjusted through output cable with 1-10V,PWM signal and Resistance



■ DIMMING OPERATION



- ※ Built-in 3 in 1 dimming function, IP67 rated. Output constant current level can be adjusted through output cable by connecting a resistance or
 1 ~ 10Vdc or 10V PWM signal between DIM+ and DIM-.
- ※ Please DO NOT connect "DIM-" to "-V".
- * Reference resistance value for output current adjustment (Typical)

Resistance value	Single driver	10ΚΩ	20ΚΩ	30ΚΩ	40ΚΩ	50ΚΩ	60ΚΩ	70ΚΩ	80ΚΩ	90ΚΩ	100ΚΩ	OPEN
	Multiple drivers	10KΩ/N	20ΚΩ/Ν	30KΩ/N	40KΩ/N	50KΩ/N	60KΩ/N	70KΩ/N	80KΩ/N	90KΩ/N	100KΩ/N	
Percentage of rated current		10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	95%~108%


※ 1 ~ 10V dimming function for output current adjustment (Typical)

	-											
Dimming	value	1V	2V	3V	4V	5V	6V	7V	8V	9V	10V	OPEN
Percenta	ge of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	95%~108%

¾ 10V PWM signal for output current adjustment (Typical): Frequency range:100Hz ~ 3KHz

Duty value	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	OPEN
Percentage of rated current	10%	20%	30%	40%	50%	60%	70%	80%	90%	100%	95%~108%


- **Using the built-in dimming function on B-type model can't turn the lighting fixture totally dark. Please refer to the connection method below to achieve 0% brightness of the lighting fixture connecting to the LED power supply unit.
- *Direct connecting to LEDs is suggested, but is not suitable for using additional drivers.



Using a switch and relay can turn ON/OFF the lighting fixture.


- 1.Output constant current level can be adjusted through output cable by connecting a resistance or 1~10Vdc or 10V PWM signal between DIM+ and DIM-.
- 2. The LED lighting fixture can be turned ON/OFF by the switch.








■ Power Factor Characteristic



■ EFFICIENCY vs LOAD (48V Model)

HBG-240 series possess superior working efficiency that up to 93% can be reached in field applications.




■ DRIVING METHODS OF LED MODULE

There are two major kinds of LED drive method "direct drive" and "with LED driver".

A typical LED power supply may either work in "constant voltage mode (CV) or constant current mode (CC)" to drive the LEDs.

Mean Well's LED power supply with CV+ CC characteristic can be operated at both CV mode (with LED driver, at area (A) and CC mode (direct drive, at area (B).



Typical LED power supply I-V curve



■ INSTALLATIONS

