Technical Data

Performance you can trust

ROCOL

TRI-Logic[®] RTD Tapping Fluid That Fortifies Cutting Fluids

TRI-Logic[®] RTD is a high performance lubricant designed for selective application on arduous operations such as reaming, tapping and drilling. The blend of lubricity and extreme pressure additives significantly reduce friction, extend tool life and improve surface finish.

TRI-Logic[®] RTD is suitable for use on a wide range of ferrous and non-ferrous materials such as stainless steel, titanium and nimonics. When used on machine tools with water mix flood applied cutting fluids the fully emulsifiable product mixes into the fluid and enhances the overall cutting performance.

Features

- Ultimate cutting performance.
- Extends tool life.
- Improves surface finish
- Reinforces water mix cutting fluids.
- Resists degradation.
- Easily removed by aqueous cleaners.
- Low odour pleasant to use.
- Contains no silicones.
- Suitable for use on CNC machines.
- Optimised for use in the TRI-Logic system.

Directions for Use

TRI-Logic[®] **RTD** should be applied directly to the cutting zone. For automatic application systems reservoirs and pipework should be drained prior to filling with **TRI-Logic**[®] **RTD**.

T +44 [0] 113 232 2600 F +44 [0] 113 232 2740 E customer-service@rocol.com www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67 Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL









BS EN ISO 9001 BS EN ISO 14001 ificate No. FM 12448 Certificate No. FMS 67596 OHSAS 18001 Certificate No. OHS 78173 INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Certific

Technical Data





TRI-Logic[®] RTD

Appearance	Clear brown liquid
Odour	Mild
Viscosity	60 cSt at 40°C
Density at 20°C	1.01 g/cm ³
Storage	Store at normal ambient temperature (5 to 30°C)
Pack Sizes – Part Codes	350 ml - 53003 5 ltr - 53006 20 ltr - 53008

Date: Jan-09

T +44 [0] 113 232 2600 F +44 [0] 113 232 2740 E customer-service@rocol.com www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67 Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL ROCOL A division of ITW Ltd





INVESTOR IN PEOPLE

BS EN ISO 9001 BS EN ISO 14001 Certificate No. FM 12448 Certificate No. EMS 67596

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.