

# TBUS8-25,0-PPPPPPPP-9005 - DIN rail bus connectors



1072478

<https://www.phoenixcontact.com/in/products/1072478>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail connector, color: black, nominal current: 6 A (parallel contacts), rated voltage (III/2): 32 V, number of positions: 8, product range: TBUS8-25..., pitch: 2.54 mm, mounting: DIN rail mounting, locking: without, mounting method: without, type of packaging: packed in cardboard, Item with gold-plated contacts, bus connectors for connecting with electronics housings, 8 parallel contacts

## Your advantages

- Space-saving installation under the housing in the DIN rail
- Contact design enables electronics modules to be easily snapped on
- Power supply and communication without additional wiring
- Parallel and serial contacts for efficient signal and data transmission

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1072478                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | *****                          |
| Product key                          | ACHAGA                         |
| GTIN                                 | 4055626765112                  |
| Weight per piece (including packing) | 6.83 g                         |
| Weight per piece (excluding packing) | 5.6 g                          |
| Customs tariff number                | 85366990                       |
| Country of origin                    | PL                             |

# TBUS8-25,0-PPPPPPPP-9005 - DIN rail bus connectors



1072478

<https://www.phoenixcontact.com/in/products/1072478>

## Technical data

### Notes

|                |   |
|----------------|---|
| Recommendation | Material of contact pads for bus connector, galvanic gold (hard gold) |
|----------------|---|

### Product properties

|                     |                    |
|---------------------|--------------------|
| Product type        | DIN rail connector |
| Product family      | TBUS8-25..         |
| Number of positions | 8                  |
| Pitch               | 2.54 mm            |

### Electrical properties

|                             |                         |
|-----------------------------|-------------------------|
| Nominal current $I_N$       | 6 A (parallel contacts) |
| Nominal voltage $U_N$       | 32 V                    |
| Rated voltage (III/3)       | 32 V                    |
| Rated surge voltage (III/3) | 1.5 kV                  |
| Rated voltage (III/2)       | 32 V                    |
| Rated surge voltage (III/2) | 1.5 kV                  |
| Rated voltage (II/2)        | 32 V                    |
| Rated surge voltage (II/2)  | 1.5 kV                  |

### Material specifications

#### Material data - contact

|                         |             |
|-------------------------|-------------|
| Contact material        | Cu alloy    |
| Surface characteristics | gold-plated |

#### Material data - housing

|  |              |
|--|--------------|
| Color (Housing)                        | black (9005) |
| Insulating material                    | PA           |
| Insulating material group              | I            |
| CTI according to IEC 60112             | 600          |
| Flammability rating according to UL 94 | V0           |

#### material specifications - connector

|          |    |
|----------|----|
| Color () | () |
|----------|----|

### Dimensions

|            |          |
|------------|----------|
| Pitch      | 2.54 mm  |
| Width [w]  | 29.3 mm  |
| Height [h] | 37.15 mm |
| Length [l] | 16.3 mm  |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

# TBUS8-25,0-PPPPPPPP-9005 - DIN rail bus connectors



1072478

<https://www.phoenixcontact.com/in/products/1072478>

## Environmental and real-life conditions

### Ambient conditions

|   |   |
|---|---|
| Ambient temperature (operation)         | -40 °C ... 105 °C (dependent on the derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                    |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                       |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                    |

## Electrical tests

### Air clearances and creepage distances |

|  |                     |
|--|---------------------|
| Specification  | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 32 V                |
| Rated surge voltage (III/3)                            | 1.5 kV              |
| minimum clearance value - non-homogenous field (III/3) | 0.8 mm              |
| minimum creepage distance (III/3)                      | 1.3 mm              |
| Rated insulation voltage (III/2)                       | 32 V                |
| Rated surge voltage (III/2)                            | 1.5 kV              |
| minimum clearance value - non-homogenous field (III/2) | 0.5 mm              |
| minimum creepage distance (III/2)                      | 0.53 mm             |
| Rated insulation voltage (II/2)                        | 32 V                |
| Rated surge voltage (II/2)                             | 1.5 kV              |
| minimum clearance value - non-homogenous field (II/2)  | 0.5 mm              |
| minimum creepage distance (II/2)                       | 0.53 mm             |

## Packaging specifications

|                      |                     |
|----------------------|---------------------|
| Type of packaging    | packed in cardboard |
| Outer packaging type | Carton              |

# TBUS8-25,0-PPPPPPPP-9005 - DIN rail bus connectors



1072478

<https://www.phoenixcontact.com/in/products/1072478>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1072478>

| cUL Recognized<br>Approval ID: E118976-20151204 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Power   | 29.9 V                | 4 A                   | -                 | -                           |
| Signal  | 29.9 V                | 4 A                   | -                 | -                           |

| UL Recognized<br>Approval ID: E118976-20151204 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Power  | 29.9 V                | 6 A                   | -                 | -                           |
| Signal   | 29.9 V                | 4 A                   | -                 | -                           |

| cULus Recognized |  |  |  |  |
|------------------|--|--|--|--|
|------------------|--|--|--|--|

# TBUS8-25,0-PPPPPPPP-9005 - DIN rail bus connectors



1072478

<https://www.phoenixcontact.com/in/products/1072478>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27460201 |
| ECLASS-12.0 | 27460201 |
| ECLASS-13.0 | 27460201 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002637 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# TBUS8-25,0-PPPPPPPP-9005 - DIN rail bus connectors



1072478  
<https://www.phoenixcontact.com/in/products/1072478>

## Environmental product compliance

|   |  |
|---|--|
| EU RoHS                                 |  |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |  |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|   | No hazardous substances above the limits |
| EU REACH SVHC                           |  |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

# TBUS8-25,0-PPPPPPPP-9005 - DIN rail bus connectors



1072478


<https://www.phoenixcontact.com/in/products/1072478>

## Accessories

### FMC 0,5/ 8-ST-2,54 - PCB connector

1821151

<https://www.phoenixcontact.com/in/products/1821151>



PCB connector, nominal cross section: 0.5 mm<sup>2</sup>, color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Au, contact connection type: Socket, number of potentials: 8, number of rows: 1, number of positions: 8, number of connections: 8, product range: FMC 0,5/...-ST, pitch: 2.54 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON FMC 0,5, locking: without, mounting method: without, type of packaging: packed in cardboard

---

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)