




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Clamp**
Packaging Method: **Bag**
Packaging Quantity: **1000**

Features

Product Type Features

Strain Relief Accessory Type	Cable Clamp
------------------------------	-------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 2295892-1
SHROUD PLASTIC


Also in the Series | MotorMan




Circular Connector Contact Inserts(2)




Connector Caps & Covers(2)




Connector Hardware(4)




Connector Seals & Cavity Plugs(2)



Connector Strain Relief(2)



Rectangular Connector Hoods & Bases (4)



Rectangular Contact Inserts(5)

Customers Also Bought



TE Part #1103436-1
HC26.Base Housing-metal



TE Part #2120330-1
METAL HOOD / KIT



TE Part #1103426-2
MALE INSERT, CRIMP, 4-POS. 22DF CONTACTS



TE Part #2120339-1
SIDE CLIP



TE Part #2295894-1
SIGNAL HOUSING



TE Part #2120432-3
CRIMP SLEEVE



TE Part #1103426-1
MALE INSERT, CRIMP, 4-POS. 22DF CONTACTS



TE Part #2120320-1
FEMALE INSERT WITH PE-CONTACT



TE Part #2120338-3
SCREEN CLAMP



TE Part #184113-1
TERM,COPALUM R 4/0A 3/0C 1/2

Documents

Product Drawings

SCREEN CLAMP; MOTORMAN SHROUD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2295891-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2295891-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2295891-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Product Specification

English