



Switches > Push Button Switches



Number of Actuators: **Single**

Illuminated: **With**

Process Sealed: **No**

Snap Action: **With**

Switch Feedback Type: **Tactile**

## Features

### Product Type Features

Illuminated	With
Actuator Style	Square Actuator

### Configuration Features

Panel Cutout Size	16 (Diameter) mm
Number of Actuators	Single
Snap Action	With
Switch Feedback Type	Tactile
Operating Function	3 NO & 3 NC, Momentary

### Electrical Characteristics

Contact Current Rating	5 A
Operating Voltage Range	20 VDC, 24 VDC

### Body Features

Product Orientation	Vertical
---------------------	----------

### Contact Features

Switch Contact Plating Material	Gold
---------------------------------	------

### Housing Features

Low Profile	No
Process Sealed	No

### Dimensions



Button Width	15 mm[.59 in]
--------------	---------------

**Industry Standards**

IP Rating	IP65
-----------	------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Customers Also Bought**



TE Part #640456-2  
02P MTA100 HDR ASSY F/L SQ STR



TE Part #640903-1  
RECEPT,PIDG FASTON 22-18 250



TE Part #881545-1  
SHUNT LP W/HANDLE 2POS 15AU



TE Part #1658621-2  
14 NOVO MIL/CTR 15DP,LEAD FREE



## Documents

### Product Drawings

164SL33=ILL SQ MOM PB W/3 NO&N

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1437569-7\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1437569-7\\_A.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1437569-7\\_A.2d\\_dxf.zip](#)

English

### 3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English