

Features

- Bevelled-edge cutter.
- Steel thickness 5 mm.
- For copper wire Ø 2.05 mm (12 awg)
- Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip.
- Anti-reflection phosphating surface treatment.
- ESD-safe handles.
- Laser marking.
- Made in Italy.

RS PRO ESD bevelled cutting edge. Medium head.

RS Stock No.: (0429727)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Made in Italy with high carbon steel and undergo a controlled atmosphere heat treatment.
- Bevelled-edge cutter for specific electronics applications.
- The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.
- The tools are joined with grounded holes and surfaces, thereby allowing precise movements.
- The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.
- ESD-safe version.

General Specifications

Cutter Type	Strong bevelled-edge cutter. Medium head.
Material	High carbon steel
ESD Safe	YES. Standard IEC 61340-5-1

Mechanical Specifications

Cutting capacities	Ø 2.05mm (12 awg) copper wire
Cutting force	12 kg
Steel thickness	5 mm
Blade angle	27°
Overall Length	138 mm
Weight	100 g

