



PROFESSIONAL RECHARGEABLE LED INSPECTION LAMP

With 2 selectable modes, this lamp features a high intensity flood inspection via 2x 1W LED and a spot beam via 1W LED torch function. The integrated magnetic back and foldable hanging hook allow a choice of mounting options.

Powered by a high capacity Lithium-ion battery, running for up to 7h per charge. Li-ion ensures maximum life performance, with low charge maintenance and no memory effect. The charging base can be mounted to walls or worktops and will recharge the lamp in under 4h.

Rechargeable and cordless light housed in heavy duty rubber casing with a virtually unbreakable polycarbonate lens, it is shock, water and oil resistant with an IP54 rating.

- 200 lumens
- 2 Light modes: High, Low
- Runtime 3h30 – 8h per charge
- Mountable charging base
- Battery charging indicator
- Integrated magnet
- Adjustable hanging hook
- IP54 Rated
- **Supplied with:** Charging base and mains adaptor
- **Used by:** Automotive, Railways, utility groups
- **Applications:** Car maintenance, machinery inspections

SPECIFICATION

Light output	200 100 lumens
Light source	3x 1W LED
Run time	3h30 Flood 7h Torch
Battery	3.6V 200m/ah Li-ion
Charge time	4h
Product size (mm)	L95 x Dia.29
Product weight (kg)	3.43
Boxed size (mm)	L275 x W176 x H69
Part no.	NS3LED

