## Features

- Loosens rusted and seized parts quickly
- Cleans and protects against rust
- Eliminates squeaks and creaks in hinges, locks, and mechanical devices
- Protects against moisture and freezing, suitable for electronics
- Removes dirt, dust, adhesives, crayons, markers, and chewing gum

# RS PRO Maintenance and Repairs Liquid

**RS Stock No.: 0802720**




RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

*Maintenance and Repairs Multi-Purpose Liquid*

- *Use: Loosens rusted parts, protects surfaces, removes dirt and creaks.*
- *Applications: Vehicles, machines, tools, home and industrial equipment.*
- *Surfaces: Metal, locks, hinges, electronic components, painted surfaces.*

## General Specifications

| | |
|---|---|
| **Package Size** | 5 l |
| **Package Type** | Canister |
| **Product Category** | Multi-Purpose Product |
| **Appearance** | Liquid |
| **Miscibility In Water** | Insoluble |
| **Odour** | Characteristic |

## Mechanical Specifications

| | |
|---|---|
| **Density At 20°C** | Not determined |
| **Purity** | Not determined |
| **Water Content** | N/A |
| **Residue On Evaporation (ppm)** | Not determined |
| **Viscosity At 20°C** | Not determined |

| | |
|---|---|
| **Evaporation Rate** | N/A |
| **Flammability** | Flammable |
| **Conductivity At 18°C** | N/A |
| **Specific Gravity At 20°C** | Not determined |
| **Non Volatiles** | N/A |
| **Active Content** | N/A |
| **pH** | N/A |
| **Inhalation Toxicity** | N/A |
| **VOC** | Not determined |
| **Vapour Pressure At 20°C** | Not determined |
| **KB Value** | Not determined |
| **PEL (PPM, 8 Hours TWA)** | N/A |
| **Total Shelf Life** | Not determined |

## Operation Environment Specifications

| | |
|---|---|
| **Boiling Point** | 187–219 °C (for liquid) |
| **Flash Point** | 43 °C (spray) / >61 °C (liquid) |
| **Freezing Point** | Not determined |
| **Service Temperature** | 5–35 °C (do not exceed 50 °C) |