

V23079A1006B301

✓ ACTIVE

TE Internal #: 2-1393788-0

TE Internal Description: V23079A1006B301

Small Signal Relay, Axicom P2 Standard

[View on TE.com >](#)



All Small Signal Relay, Axicom P2 Standard (23)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 3-1393789-8
V23079A2006B301

Customers Also Bought

TE Part #3-747579-0
SHLDNG FERRULE, PLTD, BULK PKG

TE Part #CAT-HST-RBKILS
RBK-ILS Heat Shrink Tubing

TE Part #7-1393243-5
RT424110

TE Part #6-928918-1
MQS0,63 Sn tab LL unseal. 0,2-0,35

TE Part #6-928918-3
MQS0,63 Ag tab LL unseal. 0,2-0,35

TE Part #254897-E
STVC 96 F ABC VV 7-00 TL 4,0 * 137
E007

TE Part #104113-E
ERM 125 FS 1 EE * 3,70 A-E V-V **
247

TE Part #CD80973001
ASC107468ACK0066

TE Part #104114-E
ERM 55 FS 1 EE * 3,70 A-E V-V *
TRAY 24

Documents

Product Drawings

V23079A1006B301

English

CAD Files

Customer View Model

ENG_CVM_CVM_1393788-2_A.2d_dxf.zip

English



3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1393788-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1393788-2_A.3d_stp.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-1393788-0_G1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1393788-0_G1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1393788-0_G1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Transportation, Storage, Handling, Assembly and Testing of Axicom Through Hole Terminal \(THT\) Relays](#)

English

[Transportation, Storage, Handling, Assembly and Testing of AXICOM THT Relays](#)

English

[P2 Relay Datasheet](#)

English

Product Specifications

[Definitions General Purpose Relays](#)

English

Agency Approvals

[UL](#)

English