




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Mating Area Plating Material: **Gold (Au)**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **250 VAC**

Compatible With Wire & Cable Type: **Discrete Wire**

Features

Product Type Features

Applied Pressure	Intermediate
------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Termination Resistance	12 mΩ
Dielectric Withstanding Voltage (Max)	750 V
Insulation Resistance	5000 MΩ
Operating Voltage	250 VAC

Contact Features

	100 – 200 μin
Mating Square Post Dimension	.64 mm[.025 in]
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Tin Phosphor Bronze
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Product Terminates To

Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	394.71 – 1184.12 CMA
-----------	----------------------

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Approved Standards Products	CSA LR7189, UL E28476
---	-----------------------

Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	5000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 843996-3
TOOL, EXTRACTION RESET

TE Part # 91516-1
CCII MOD IV REC 30-20 ASSY

Also in the Series | AMPMODU IV/V

Backplane Connector Housings(1)

Connector Caps & Covers(11)

Connector Contacts(271)

Connector Hardware(10)

Insertion & Extraction Tools(4)

PCB Headers & Receptacles(517)

Power Contacts(207)

Customers Also Bought

TE Part #1-104479-2
SHORT POINT RECP CONT LP

TE Part #170363-3
MINI UNIVERSAL M-N-L PIN LP

TE Part #2-330648-1
PIDG 22-16 22-18 MIL R 4; TAPE


TE Part #2-520263-4
ULTRA-FAST 250 ASY REC 22-18 TPBR



TE Part #2-2176230-4
3522 68R 5% 3W



TE Part #172344-1
MINI UNIVERSAL MATE-N-LOK CAP HOUSING 3P




TE Part #205202-7
PIN CONTACT L.P.



TE Part #CONREVSMA010
RP-SMA Jack to RP-SMA Plug RA



TE Part #30927
TERMINAL,DG R 16-14 8



TE Part #811945-000
202K121-12-0

Documents

Product Drawings

MOD IV RECP LP, 30 Au, TIN, RoHS

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_2-87195-6_M.2d_dxf.zip

English

Customer View Model

ENG_CVM_2-87195-6_M.3d_igs.zip

English

Customer View Model

ENG_CVM_2-87195-6_M.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English