


Features

- **Heavy-Duty Steel Construction** – Built from high-quality steel for superior strength in industrial settings.
- **Rust-Resistant Finish** – Red powder coating offers enhanced corrosion resistance for long-term use.
- **Quick & Secure Installation** – Single-piece design allows for easy sliding over valve handles to lock in the off position.
- **Versatile Valve Fit** – Compatible with ball valve handles ranging from ¼" (6.35mm) to 1" (25mm).
- **Padlock Compatibility** – Accepts padlocks with up to 9mm shackle diameter to ensure tamper-proof lockout.
- **Ideal for Tight Spaces** – Especially effective for hard-to-reach or compact piping systems.

RS PRO One Piece Steel - Small Ball Valve Lockout with 8 Lock Provision

RS Stock No.: 0710510



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *Constructed from industrial-grade steel with a red powder-coated finish for durability and corrosion resistance.*
- *Simple, single-piece sliding mechanism enables fast and secure lockout of ball valve handles.*
- *Designed to accommodate valves with diameters from ¼" (6.35mm) to 1" (25mm), offering broad compatibility.*
- *Prevents unauthorised access to ball valves during maintenance or repair operations.*
- *Can be used with safety padlocks having shackles up to 9mm diameter.*
- *Perfect for applications involving hard-to-access pipelines or confined workspaces.*

General Specifications

Type	Ball Valve Lockout
Material	Steel with red powder coat finish
Colour	Red
Padlock holes	08
Package	PE-LD

Mechanical Specifications

Dimensions	140mm X 53mm
Length	140mm
Width	53mm
Max Shackle Dia	6.5mm
Max Handle Thickness	7mm
Max Handle Width	37mm
Weight	88 Grams

Operation Environment Specifications

Withstand temperature	-30°C to +93°C (-20°F to +200°F)
------------------------------	----------------------------------