

Product data sheet

Specifications



Repacked, impulse relay, Acti9 iTL, 4P, 16A, 4 NO, 110VDC, 230VAC to 240VAC, 50Hz to 60Hz

A9C30814W



This repacked option saves 1.482 over the standard condition

Main

range of product	Acti9
Product name	Acti9 iTL
Product or component type	Impulse relay
Device short name	iTL
Device application	Standard
Poles	4P
Pole contact composition	4 NO
[In] rated current	16 A
Network type	AC
[Uc] control circuit voltage	230...240 V AC 50/60 Hz 110 V DC

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
Control type	Remote and manual control
Control signal type	Impulse
Switching frequency	5 switching operations/minute 100 switching operations/day
Impulse duration	50 ms...1 s
Remote control type	Illuminated push-button 3 mA
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	4
Height	84 mm
Width	36 mm
Depth	60 mm
Electrical durability	AC-21: 200000 cycles AC-22: 100000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - terminals	Control circuit: tunnel type terminals 1 cable(s) 0.5...4 mm² rigid Control circuit: tunnel type terminals 1 cable(s) 0.5...4 mm² rigid with cable end Control circuit: tunnel type terminals 1 cable(s) 1...4 mm² flexible Control circuit: tunnel type terminals 1 cable(s) 1...4 mm² flexible with ferrule Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² rigid Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² rigid with cable end Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² flexible Power circuit: tunnel type terminals 1 cable(s) 1.5...4 mm² flexible with ferrule
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti9 iATeT Acti9 iATL4 Acti9 iATLc Acti9 iATLc+s Acti9 iATLm Acti9 iATLs Acti9 iATLz Acti9 iETL iTL 16 Acti9 iATLc+c Acti9 iATL24

Environment

Standards	EN 669-1 EN 669-2-2
Product certifications	GOST CCC
Quality labels	KEMA CEBEC NF VDE IMQ
Noise level	60 dB
IP degree of protection	IP20 conforming to IEC 60529 (on opening) IP40 conforming to IEC 60529 (in enclosure)
Pollution degree	3
Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	8.400 cm
Package 1 Length	12.800 cm
Package 1 Weight	242.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	12
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm

Package 2 Weight	3.092 kg
------------------	----------

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

1 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

429095ee-388a-4184-bea4-16f87e374975

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins