

Technical data



2315SKC3

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, tapered bore, open

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	75 mm
D - External diameter	160 mm
B - Bearing/Inner ring width	55 mm
rs - Min fillet radius	2,1 mm
Associated sleeve reference	H2315X
Radial clearance class	C3
Precision class	P0
Mass	4,78 kg

PRODUCT PERFORMANCE

C - Dynamic load	125000000 mN
C0 - Static load	43000000 mN
Cu - Fatigue limit load	1800000 mN
e - Coefficient	0.38
Y0 - Static axial load coefficient	1.7
Y1 - Lower axial load coefficient	1.6
Y2 - Upper axial load coefficient	2.5
N lim - Oil lubrication limit speed	25800 °/s
N lim - Grease lubrication limit speed	20400 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	86 mm
-----------------------------------	-------



2315SKC3

Double-row self-aligning ball bearings

ABUTMENT	
da max - Max shoulder diameter IR	96 mm
db - Min diameter for Sleeve	82 mm
Ce - Min length fro Sleeve	5 mm
Da max - Max shoulder diameter OR	149 mm
ra max - Max shaft & housing fillet radius	2 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15