

8564-01

### Torque wrench DREMOMETER

750-2000 Nm

Code	ETIM
<b>7695250</b>	<b>EC002132</b>
EAN	UNSPSC
<b>4002805856413</b>	<b>27-11-17-15</b>
Country of origin	eCl@ss
<b>Germany</b>	<b>21-04-02-22</b>
Customs tariff number	
<b>82041100</b>	



### Article description

- Use:  
Controlled screw tightening in the range of 750 - 2000 Nm
- For use in almost all industrial manufacturing areas
- Features:  
Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- 1" square drive with pin-locking mechanism DIN 3120 - B 25, ISO 1174
- Automatic short-path actuation with tactile impulse and audible signal
- Single scale with a scale graduation of 50 Nm
- Technical advantage/Function:  
Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
- No inaccuracies whether used with both hands or held away from the handle (as for standard torque wrenches)
- Both the square drive and fulcrum are on an axis which ensures a high degree of user safety; can be extended to reduce the user's working load.
- Extremely low wear attributable to reduced forces in a lever mechanism
- Forged lever chain from our group own quality forge
- Maximum precision even when subjected to extreme continuous use
- Long life cycles and tool lives • Easy operation - fast and safe torque tightening
- Easy adjustment thanks to attractive adjusting button secured against loss at the end of the handle
- Single- and double-square drive for controlled bi-directional tightening

### Article parts list

Extension tube ,8564-92,8572-74

### Article information

Contents (Qty of pieces)	<b>1</b>	Trigger mechanism	<b>Short path triggering</b>
Net weight [kg]	<b>12 kg</b>	Precision +/-	<b>+/- 3 %</b>
Total length [mm]	<b>932 mm</b>	Direction of tightening	<b>Right</b>
Total width [mm]	<b>60 mm</b>	Fixed setting	<b>no</b>
Total height [mm]	<b>71 mm</b>	Test certificate	<b>DIN EN ISO 6789-2:2017</b>
Material	<b>Aluminum alloy</b>	Head height 1 [mm]	<b>40 mm</b>
Standard	<b>DIN 3120 - B 25</b> <b>ISO 1174</b>	Width of head 1 [mm]	<b>60,0 mm</b>
Drive connector square (male)	<b>1"</b>	Torque wrench type	<b>E</b>
Drive connector square (male)	<b>25 mm</b>	Calibration length	<b>2213 mm</b>
Drive type/drive	<b>Single square rigid</b>	Graduation [N·m]	<b>50 Nm</b>
Torque (min.) [N·m]	<b>750 Nm</b>	Distance housing - square drive	<b>30 mm</b>
Torque (max.) [N·m]	<b>2000 Nm</b>	Storage/Content	<b>Box</b>
Torque range (min./max.) [N·m]	<b>750 Nm - 2000 Nm</b>	Length of extension tube 1	<b>925 mm</b>
Torque range (min./max.) [lbf·ft]	-	Length of slip-on tube 2	<b>745 mm</b>